

# NI Serial Hardware Specifications Guide

This document lists safety and compliance information for NI Serial hardware, as well as physical specifications, software characteristics, and recommended operating conditions.

## Contents

---

Safety and Electromagnetic Compatibility .....	1
PCI Serial Hardware .....	5
PCI Express Serial Hardware.....	14
PXI Serial Hardware .....	18
USB Serial Hardware.....	28
ENET Serial Hardware .....	32
ExpressCard Serial Hardware .....	35
PCMCIA Serial Hardware .....	38
Where to Go for Support.....	42

## Safety and Electromagnetic Compatibility

---

This section contains safety instructions and electromagnetic compatibility (EMC) information for the hardware it accompanies. Read this section before installing and using the new hardware.

### Safety Information

The following section contains important safety information that you must follow when installing and using the hardware.

Do not operate the hardware in a manner not specified in this document and in the user documentation. Misuse of the hardware can result in a hazard. You can compromise the safety protection if the hardware is damaged in any way. If the hardware is damaged, return it to National Instruments for repair.

Clean the hardware with a soft, nonmetallic brush. Make sure that the hardware is completely dry and free from contaminants before returning it to service.

Do not substitute parts or modify the hardware except as described in this document. Use the hardware only with the chassis, modules, accessories, and cables specified in the installation instructions or specifications. You must have all covers and filler panels installed during operation of the hardware.

Do not operate the hardware in an explosive atmosphere or where there may be flammable gases or fumes unless the hardware is UL (U.S.) or Ex (EU) Certified and marked for hazardous locations. The hardware must be in a suitably rated IP 54 minimum enclosure for hazardous locations. Refer to the hardware's user documentation for more information.

You must insulate signal connections for the maximum voltage for which the hardware is rated. Do not exceed the maximum ratings for the hardware. Do not install wiring while the hardware is live with electrical signals. Do not remove or add connector blocks when power is connected to the system. Avoid contact between your body and the connector block signal when hot swapping hardware. Remove power from signal lines before connecting them to or disconnecting them from the hardware.

Operate the hardware only at or below Pollution Degree 2. Pollution is foreign matter in a solid, liquid, or gaseous state that can reduce dielectric strength or surface resistivity. The following is a description of pollution degrees:

- Pollution Degree 1 means no pollution or only dry, nonconductive pollution occurs. The pollution has no influence. Typical level for sealed components or coated PCBs.
- Pollution Degree 2 means that only nonconductive pollution occurs in most cases. Occasionally, however, a temporary conductivity caused by condensation must be expected. Typical level for most products.
- Pollution Degree 3 means that conductive pollution occurs, or dry, nonconductive pollution occurs that becomes conductive due to condensation.

Operate the hardware at or below the measurement category<sup>1</sup> marked on the hardware label. Measurement circuits are subjected to working voltages<sup>2</sup> and transient stresses (overvoltage) from the circuit to which they are connected during measurement or test. Measurement categories establish standard impulse withstand voltage levels that commonly occur in electrical distribution systems. The following is a description of measurement categories:

- Measurement Category I is for measurements performed on circuits not directly connected to the electrical distribution system referred to as MAINS<sup>3</sup> voltage. This category is for measurements of voltages from specially protected secondary circuits. Such voltage measurements include signal levels, special hardware, limited-energy parts of hardware, circuits powered by regulated low-voltage sources, and electronics.
- Measurement Category II is for measurements performed on circuits directly connected to the electrical distribution system (MAINS<sup>3</sup>). This category refers to local-level electrical distribution, such as that provided by a standard wall outlet (for example, 115 AC voltage for U.S. or 230 AC voltage for Europe). Examples of Measurement Category II are measurements performed on household appliances, portable tools, and similar hardware.
- Measurement Category III is for measurements performed in the building installation at the distribution level. This category refers to measurements on hard-wired hardware such as hardware in fixed installations, distribution boards, and circuit breakers. Other examples are wiring, including cables, bus bars, junction boxes, switches, socket outlets in the fixed installation, and stationary motors with permanent connections to fixed installations.
- Measurement Category IV is for measurements performed at the primary electrical supply installation typically outside buildings. Examples include electricity meters and measurements on primary overcurrent protection devices and on ripple control units.

To obtain the safety certification(s) for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

---

<sup>1</sup> Measurement categories, also referred to as overvoltage or installation categories, are defined in electrical safety standard IEC 61010-1 and IEC 60664-1.

<sup>2</sup> Working voltage is the highest rms value of an AC or DC voltage that can occur across any particular insulation.

<sup>3</sup> MAINS is defined as a hazardous live electrical supply system that powers hardware. Suitably rated measuring circuits may be connected to the MAINS for measuring purposes.

# Electromagnetic Compatibility Information

This hardware has been tested and found to comply with the applicable regulatory requirements and limits for electromagnetic compatibility (EMC) as indicated in the hardware's Declaration of Conformity (DoC)<sup>1</sup>. These requirements and limits are designed to provide reasonable protection against harmful interference when the hardware is operated in the intended electromagnetic environment. In special cases, for example when either highly sensitive or noisy hardware is being used in close proximity, additional mitigation measures may have to be employed to minimize the potential for electromagnetic interference.

While this hardware is compliant with the applicable regulatory EMC requirements, there is no guarantee that interference will not occur in a particular installation. To minimize the potential for the hardware to cause interference to radio and television reception or to experience unacceptable performance degradation, install and use this hardware in strict accordance with the instructions in the hardware documentation and the DoC<sup>1</sup>.

If this hardware does cause interference with licensed radio communications services or other nearby electronics, which can be determined by turning the hardware off and on, you are encouraged to try to correct the interference by one or more of the following measures:

- Reorient the antenna of the receiver (the device suffering interference).
- Relocate the transmitter (the device generating interference) with respect to the receiver.
- Plug the transmitter into a different outlet so that the transmitter and the receiver are on different branch circuits.

Some hardware may require the use of a metal, shielded enclosure (windowless version) to meet the EMC requirements for special EMC environments such as, for marine use or in heavy industrial areas. Refer to the hardware's user documentation and the DoC<sup>1</sup> for product installation requirements.

When the hardware is connected to a test object or to test leads, the system may become more sensitive to disturbances or may cause interference in the local electromagnetic environment.

Operation of this hardware in a residential area is likely to cause harmful interference. Users are required to correct the interference at their own expense or cease operation of the hardware.

Changes or modifications not expressly approved by National Instruments could void the user's right to operate the hardware under the local regulatory rules.

---

<sup>1</sup> The Declaration of Conformity (DoC) contains important EMC compliance information and instructions for the user or installer. To obtain the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

# PCI Serial Hardware

---

This section describes the characteristics of the PCI serial hardware and the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

## Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

## CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息, 请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## PCI-843x Series Hardware

### Nonisolated PCI Two-Port Boards

Dimensions .....10.67 × 14.22 cm  
(4.2 × 5.6 in.)

I/O connector .....DB-9 male connector

Power requirement (from PCI channel)

PCI-8430/2

+5 VDC .....325 mA typical  
500 mA maximum

PCI-8431/2

+5 VDC .....500 mA typical  
700 mA maximum

Weight

PCI-8430/2.....	88 g
PCI-8431/2.....	92 g

## Nonisolated PCI Four-Port Boards

Dimensions.....	10.67 × 14.22 cm (4.2 × 5.6 in.)
-----------------	-------------------------------------

I/O connector <sup>1</sup> .....	10-position modular jack
----------------------------------	--------------------------

Power requirement (from PCI channel)

PCI-8430/4

+5 VDC.....	400 mA typical 600 mA maximum
-------------	----------------------------------

PCI-8431/4

+5 VDC.....	725 mA typical 1.1 A maximum
-------------	---------------------------------

Weight

PCI-8430/4.....	99 g
PCI-8431/4.....	102 g

## Nonisolated PCI Eight-Port Boards

Dimensions.....	10.67 × 14.48 cm (4.2 × 5.7 in.)
-----------------	-------------------------------------

I/O connector <sup>2</sup> .....	68-position, SCSI type connector
----------------------------------	----------------------------------

Power requirement (from PCI channel)

PCI-8430/8

+5 VDC.....	600 mA typical 900 mA maximum
-------------	----------------------------------

PCI-8431/8

+5 VDC.....	1.3 A typical 1.9 A maximum
-------------	--------------------------------

Weight

PCI-8430/8.....	84 g
PCI-8431/8.....	85 g

---

<sup>1</sup> The four-port PCI serial boards require cables, included in your kit, to convert the 10-position modular jacks to DB-9 male connectors.

<sup>2</sup> The eight-port PCI serial boards require a cable, included in your kit, to convert the 68-position connector to eight DB-9 connectors.

## Nonisolated PCI 16-Port Boards

Dimensions .....	10.67 × 17.52 cm (4.2 × 6.9 in.)
I/O connector <sup>1</sup> .....	68-position, VHDCI × 2
Power requirement (from PCI channel)	
PCI-8430/16	
+5 VDC .....	935 mA typical 1.4 A maximum
Weight .....	99 g

## Isolated PCI Two-Port Boards

Dimensions .....	10.67 × 17.52 cm (4.2 × 6.9 in.)
I/O connector .....	DB-9 male connector
Operating rated voltage (continuous)	
RS-232 .....	-25 V to +25 V
RS-485 .....	-7 V to +12 V
Isolation voltages	
Port-to-port	
Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test
Port-to-host	
Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test
Power requirement (from PCI channel)	
PCI-8432/2	
+5 VDC .....	380 mA typical 570 mA maximum
PCI-8433/2	
+5 VDC .....	380 mA typical 570 mA maximum

---

<sup>1</sup> The 16-port PCI serial boards require two cables, included in your kit, to convert the two 68-position connectors to the 16 (2 × 8) DB-9 male connectors.



## Weight

PCI-8432/2.....	102 g
PCI-8433/2.....	104 g

## Isolated PCI Four-Port Boards

Dimensions.....	10.67 × 17.44 cm (4.2 × 6.9 in.)
-----------------	-------------------------------------

I/O connector <sup>1</sup> .....	10-position modular jack
----------------------------------	--------------------------

### Operating rated voltage (continuous)

RS-232.....	-25 V to +25 V
RS-485.....	-7 V to +12 V

### Isolation voltages

#### Port-to-port

Continuous.....	60 VDC (CAT I)
Withstand.....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

#### Port-to-host

Continuous.....	60 VDC (CAT I)
Withstand.....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

### Power requirement (from PCI channel)

#### PCI-8432/4

+5 VDC.....	550 mA typical 815 mA maximum
-------------	----------------------------------

#### PCI-8433/4

+5 VDC.....	785 mA typical 1.2 A maximum
-------------	---------------------------------

## Weight

PCI-8432/4.....	105 g
PCI-8433/4.....	106 g

---

<sup>1</sup> The four-port PCI serial boards require cables, included in your kit, to convert the 10-position modular jacks to DB-9 male connectors.

# Legacy PCI Hardware

## Nonisolated PCI Two-Port Boards

Dimensions .....	10.67 × 14.22 cm (4.2 × 5.6 in.)
I/O connector .....	DB-9 male connector
Power requirement (from PCI channel)	
PCI-485/2	
+5 VDC .....	350 mA typical 750 mA maximum
PCI-232/2	
+5 VDC .....	50 mA typical 100 mA maximum
±12 VDC .....	20 mA typical 200 mA maximum

## Nonisolated PCI Four-Port Boards

Dimensions .....	10.67 × 14.22 cm (4.2 × 5.6 in.)
I/O connector <sup>1</sup> .....	10-position modular jack
Power requirement (from PCI channel)	
PCI-485/4	
+5 VDC .....	700 mA typical 1.3 A maximum
PCI-232/4	
+5 VDC .....	70 mA typical 150 mA maximum
±12 VDC .....	40 mA typical 400 mA maximum

---

<sup>1</sup> The four-port legacy PCI serial boards require a cable to convert the 10-position modular jack to either DB-9 or DB-25 male connectors.

## Nonisolated PCI Eight-Port Boards

Dimensions.....	10.67 × 14.48 cm (4.2 × 5.7 in.)
I/O connector <sup>1</sup> .....	68-position, SCSI type connector
Power requirement (from PCI channel)	
PCI-485/8	
+5 VDC.....	1.1 A typical 2.0 A maximum
PCI-232/8	
+5 VDC.....	100 mA typical 180 mA maximum
±12 VDC.....	80 mA typical 800 mA maximum

## Nonisolated PCI 16-Port Boards

Dimensions.....	10.67 × 17.52 cm (4.2 × 6.9 in.)
I/O connector <sup>2</sup> .....	100-position, SCSI type connector
Power requirement (from PCI channel)	
PCI-232/16	
+5 VDC.....	250 mA typical 500 mA maximum

## Isolated PCI Two-Port Boards

Dimensions.....	10.67 × 17.52 cm (4.2 × 6.9 in.)
I/O connector.....	DB-9 male connector
Operating rated voltage (continuous)	
RS-232 .....	-25 V to +25 V
RS-485 .....	-7 V to +12 V

---

<sup>1</sup> The eight-port legacy PCI serial boards require a cable, included in your kit, to convert the 68-position connector to eight DB-9 male connectors.

<sup>2</sup> The 16-port legacy PCI serial boards require a breakout box, included in your kit, to separate the 100-position connector to 16 DB-9 male connectors.

## Isolation voltages

### Port-to-port

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

### Port-to-host

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

## Power requirement (from PCI channel)

### PCI-485/2

+5 VDC .....	800 mA typical 1.3 A maximum
--------------	---------------------------------

### PCI-232/2

+5 VDC .....	400 mA typical 650 mA maximum
--------------	----------------------------------

## Isolated PCI Four-Port Boards

Dimensions .....	10.67 × 17.44 cm (4.2 × 6.9 in.)
------------------	-------------------------------------

I/O connector <sup>1</sup> .....	10-position modular jack
----------------------------------	--------------------------

## Operating rated voltage (continuous)

RS-232 .....	-25 V to +25 V
RS-485 .....	-7 V to +12 V

## Isolation voltages

### Port-to-port

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

### Port-to-host

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

---

<sup>1</sup> The four-port legacy PCI serial boards require a cable to convert the 10-position modular jack to either DB-9 or DB-25 male connectors.

## Power requirement (from PCI channel)

### PCI-485/4

+5 VDC..... 1.0 A typical  
1.5 A maximum

### PCI-232/4

+5 VDC..... 500 mA typical  
750 mA maximum

## Environmental Characteristics

### Operating Environment

Ambient temperature..... 0 to 55 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 10 to 90%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

Altitude (maximum)..... 2,000 m

Indoor use only.

### Storage Environment

Ambient temperature..... -20 to 70 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 5 to 95%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

## Other Specifications

### Maximum cable length

RS-485<sup>1</sup> ..... 30 m (limited by EMC/surge)  
RS-232 ..... 2,500 pF equivalent  
(TIA-EIA-232-F 2.1.4)

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

Data line ESD protection (human body model)	
RS-485 .....	±15 kV
RS-232 .....	±15 kV

## PCI Express Serial Hardware

---

This section describes the characteristics of the PCI Express serial hardware and the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

### Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

### Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

### CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## NI PCIe-843x Series Hardware

### Nonisolated PCI Express 16-Port Boards

Dimensions (without bracket) ..... 11.12 × 17.53 cm (4.38 × 6.9 in.)

I/O connectors

NI PCIe-8430/16

RS-232<sup>1</sup> ..... 68-position VHDCI × 2

PCI Express ..... x1

---

<sup>1</sup> The 16-port PCI Express serial boards require two cables, included in your kit, to convert the two 68-position connectors to the 16 (2 × 8) DB-9 male connectors.

NI PCIe-8431/16	
RS-485 <sup>1</sup> .....	68-position VHDCI × 2
PCI Express .....	x1

Power requirement (from PCI Express channel)

NI PCIe-8430/16	
+3.3 VDC .....	400 mA typical 1.5 A maximum
+12 VDC .....	210 mA typical 250 mA maximum
NI PCIe-8431/16	
+3.3 VDC <sup>2</sup> .....	1.4 A typical, 3 A maximum
+12 VDC .....	210 mA typical 250 mA maximum

Weight

NI PCIe-8430/16 .....	99 g
NI PCIe-8431/16 .....	101 g

## Nonisolated PCI Express 8-Port Boards

Dimensions (without bracket) ..... 11.12 × 17.53 cm (4.38 × 6.9 in.)

I/O connectors

NI PCIe-8430/8	
RS-232 <sup>3</sup> .....	68-position VHDCI
PCI Express .....	x1
NI PCIe-8431/8	
RS-485 <sup>3</sup> .....	68-position VHDCI
PCI Express .....	x1

Power requirement (from PCI Express channel)

NI PCIe-8430/8	
+3.3 VDC <sup>4</sup> .....	200 mA typical 750 mA maximum
+12 VDC .....	190 mA typical 220 mA maximum

<sup>1</sup> The 16-port PCI Express serial boards require two cables, included in your kit, to convert the two 68-position connectors to the 16 (2 × 8) DB-9 male connectors.

<sup>2</sup> These values are based on the assumption that all 16 ports (for the PCIe-8431/16) or 8 ports (for the PCIe-8431/8) are using a 620 Ω bias resistor and NI-offered terminators installed on both ends of the cable.

<sup>3</sup> The 8-port PCI Express serial boards require a cable, included in your kit, to convert the 68-position connector to eight DB-9 male connectors.

<sup>4</sup> These values are based on the assumption that all 16 ports (for the PCIe-8431/16) or 8 ports (for the PCIe-8431/8) are using a 620 Ω bias resistor and NI-offered terminators installed on both ends of the cable.



NI PCIe-8431/8	
+3.3 VDC.....	700 mA typical 1.5 A maximum
+12 VDC.....	190 mA typical 220 mA maximum

**Weight**

NI PCIe-8430/8.....	88 g
NI PCIe-8431/8.....	90 g

**Environmental Characteristics**

**Operating Environment**

Ambient temperature.....	0 to 55 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)
Relative humidity .....	10 to 90%, noncondensing (Tested in accordance with IEC-60068-2-56.)
Altitude (maximum).....	2,000 m

**Storage Environment**

Ambient temperature.....	-20 to 70 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)
Relative humidity .....	5 to 95%, noncondensing (Tested in accordance with IEC-60068-2-56.)

**Other Specifications**

Maximum cable length	
RS-485 <sup>1</sup> .....	30 m (limited by EMC/surge)
RS-232 .....	2,500 pF equivalent (TIA-EIA-232-F 2.1.4)
Data line ESD protection (human body model)	
RS-485 .....	±15 kV
RS-232 .....	±15 kV

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

# PXI Serial Hardware

---

This section describes the characteristics of the PXI serial hardware and the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

## Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

## CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息, 请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## PXI-843x Serial Hardware

### Nonisolated PXI Two-Port Boards

Dimensions..... 100 × 160 mm  
(3.94 × 6.37 in.)

I/O connector..... DB-9 male connector

Power requirement (from PXI channel)

PXI-8430/2

+5 VDC..... 325 mA typical  
500 mA maximum

PXI-8431/2

+5 VDC..... 500 mA typical  
750 mA maximum

Weight

PXI-8430/2 .....	134 g
PXI-8431/2 .....	134 g

### Nonisolated PXI Four-Port Boards

Dimensions .....	100 × 160 mm (3.94 × 6.37 in.)
------------------	-----------------------------------

I/O connector <sup>1</sup> .....	10-position modular jack
----------------------------------	--------------------------

Power requirement (from PXI channel)

PXI-8430/4

+5 VDC .....	400 mA typical 600 mA maximum
--------------	----------------------------------

PXI-8431/4

+5 VDC .....	725 mA typical 1.1 A maximum
--------------	---------------------------------

Weight

PXI-8430/4 .....	137 g
PXI-8431/4 .....	140 g

### Nonisolated PXI Eight-Port Boards

Dimensions .....	100 × 160 mm (3.94 × 6.37 in.), 3U
------------------	---------------------------------------

I/O connector <sup>2</sup> .....	68-position SCSI (68-pin SCSI to eight DB-9 male connector adapter cable included)
----------------------------------	--

Power requirement (from PXI channel)

PXI-8430/8

+5 VDC .....	1 A typical 1.5 A maximum
--------------	------------------------------

PXI-8431/8

+5 VDC .....	925 mA typical 1.4 A maximum
--------------	---------------------------------

---

<sup>1</sup> The four-port PXI serial boards require cables, included in your kit, to convert the 10-position modular jacks to DB-9 male connectors.

<sup>2</sup> The eight-port PXI serial boards require a cable, included in your kit, to convert the 68-position connector to eight DB-9 connectors.

## Weight

PXI-8430/8.....	135 g
PXI-8431/8.....	137 g

## Nonisolated PXI 16-Port Boards

Dimensions.....	100 × 160 mm (3.94 × 6.37 in.), 3U
I/O connector <sup>1</sup> .....	68-position VHDCI × 2
Power requirement (from PXI channel)	
PXI-8430/16	
+5 VDC.....	935 mA typical 1.4 A maximum
Weight.....	157 g

## Isolated PXI Two-Port Boards

Dimensions.....	100 × 160 mm (3.94 × 6.37 in.), 3U
I/O connector.....	DB-9 male connector × 2
Operating rated voltage (continuous)	
RS-232 .....	–25 V to +25 V
RS-485 .....	–7 V to + 12 V
Isolation voltages	
Port-to-port	
Continuous.....	60 VDC (CAT I)
Withstand.....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test
Port-to-host	
Continuous.....	60 VDC (CAT I)
Withstand.....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

---

<sup>1</sup> The 16-port PXI serial boards require two cables, included in your kit, to convert the two 68-position connectors to the 16 (2 × 8) DB-9 male connectors.

Power requirement (from PXI channel)

PXI-8432/2

+5 VDC .....725 mA typical  
1 A maximum

PXI-8433/2

+5 VDC .....725 mA typical  
1 A maximum

Weight

PXI-8432/2 .....125 g

PXI-8433/2 .....125 g

## Isolated PXI Four-Port Boards

Dimensions .....100 × 160 mm  
(3.94 × 6.37 in.), 3U

I/O connector<sup>1</sup> .....10-position modular jack  
(RJ-50) × 4

Operating rated voltage (continuous)

RS-232 .....–25 V to +25 V

RS-485 .....–7 V to +12 V

Isolation voltages

Port-to-port

Continuous .....60 VDC (CAT I)

Withstand .....2000 V<sub>rms</sub>, verified by a 5 s  
dielectric withstand test

Port-to-host

Continuous .....60 VDC (CAT I)

Withstand .....2000 V<sub>rms</sub>, verified by a 5 s  
dielectric withstand test

Power requirement (from PXI channel)

PXI-8432/4

+5 VDC .....925 mA typical  
2 A maximum

PXI-8433/4

+5 VDC .....950 mA typical  
2 A maximum

---

<sup>1</sup> The four-port PXI serial boards require cables, included in your kit, to convert the 10-position modular jacks to DB-9 male connectors.

## Weight

PXI-8432/4.....	147 g
PXI-8433/4.....	147 g

## Environmental Characteristics

### Operating Environment

Ambient temperature..... 0 to 55 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 10 to 90%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

Altitude (maximum)..... 2,000 m

Indoor use only.

### Storage Environment

Ambient temperature..... -20 to 70 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 5 to 95%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

### Other Specifications

#### Maximum cable length

RS-485 <sup>1</sup> .....	30 m (limited by EMC/surge)
RS-232 .....	2,500 pF equivalent (TIA-EIA-232-F 2.1.4)

#### Data line ESD protection (human body model)

RS-485 .....	±15 kV
RS-232 .....	±15 kV

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

# Legacy PXI Serial Hardware

## Nonisolated PXI Two-Port Boards

Dimensions .....100 × 160 mm  
(3.94 × 6.37 in.)

I/O connector .....DB-9 male connector

Power requirement (from PXI channel)

PXI-8420/2

+5 VDC .....100 mA typical  
150 mA maximum

±12 VDC .....20 mA typical  
200 mA maximum

PXI-8421/2

+5 VDC .....350 mA typical  
750 mA maximum

## Nonisolated PXI Four-Port Boards

Dimensions .....100 × 160 mm  
(3.94 × 6.37 in.)

I/O connector<sup>1</sup> .....10-position modular jack

Power requirement (from PXI channel)

PXI-8420/4

+5 VDC .....125 mA typical  
200 mA maximum

±12 VDC .....40 mA typical  
400 mA maximum

PXI-8421/4

+5 VDC .....350 mA typical  
750 mA maximum

---

<sup>1</sup> The four-port legacy PXI serial boards require a cable to convert the 10-position modular jack to either DB-9 or DB-25 male connectors.



## Nonisolated PXI Eight-Port Boards

Dimensions.....	100 × 160 mm (3.94 × 6.37 in.)
I/O connector <sup>1</sup> .....	68-position, SCSI type connector
Power requirement (from PXI channel)	
PXI-8420/8	
+5 VDC.....	150 mA typical 250 mA maximum
±12 VDC.....	80 mA typical 800 mA maximum
PXI-8421/8	
+5 VDC.....	1.1 A typical 2.0 A maximum

## Nonisolated PXI 16-Port Boards

Dimensions.....	100 × 160 mm (3.94 × 6.37 in.)
I/O connector <sup>2</sup> .....	100-position, SCSI type connector
Power requirement (from PXI channel)	
PXI-8420/16	
+5 VDC.....	500 mA typical 750 mA maximum

## Isolated PXI Two-Port Boards

Dimensions.....	100 × 160 mm (3.94 × 6.37 in.)
I/O connector.....	DB-9 male connector
Operating rated voltage (continuous)	
RS-232 .....	-25 V to +25 V
RS-485 .....	-7 V to +12 V

---

<sup>1</sup> The eight-port legacy PXI serial boards require a cable, included in your kit, to convert the 68-position connector to eight DB-9 male connectors.

<sup>2</sup> The 16-port legacy PXI serial boards require a breakout box, included in your kit, to separate the 100-position connector to 16 DB-9 male connectors.

## Isolation voltages

### Port-to-port

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

### Port-to-host

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

## Power requirement (from PXI channel)

### PXI-8422/2

+5 VDC .....	400 mA typical 650 mA maximum
--------------	----------------------------------

### PXI-8423/2

+5 VDC .....	800 mA typical, 1.3 A maximum
--------------	-------------------------------

## Isolated PXI Four-Port Boards

Dimensions .....	100 × 160 mm (3.94 × 6.37 in.)
------------------	-----------------------------------

I/O connector <sup>1</sup> .....	10-position modular jack
----------------------------------	--------------------------

## Operating rated voltage (continuous)

RS-232 .....	-25 V to +25 V
RS-485 .....	-7 V to +12 V

## Isolation voltages

### Port-to-port

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

### Port-to-host

Continuous .....	60 VDC (CAT I)
Withstand .....	2000 V <sub>rms</sub> , verified by a 5 s dielectric withstand test

---

<sup>1</sup> The four-port legacy PXI serial boards require a cable to convert the 10-position modular jack to either DB-9 or DB-25 male connectors.

## Power requirement (from PXI channel)

### PXI-8422/4

+5 VDC..... 500 mA typical  
750 mA maximum

### PXI-8423/4

+5 VDC..... 1.0 A typical  
1.5 A maximum

## Environmental Characteristics

### Operating Environment

Ambient temperature..... 0 to 55 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 10 to 90%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

Altitude (maximum)..... 2,000 m

Indoor use only.

### Storage Environment

Ambient temperature..... -20 to 70 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 5 to 95%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

## Other Specifications

### Maximum cable length

RS-485<sup>1</sup> ..... 30 m (limited by EMC/surge)  
RS-232 ..... 2,500 pF equivalent  
(TIA-EIA-232-F 2.1.4)

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

Data line ESD protection (human body model)	
RS-485 .....	±15 kV
RS-232 .....	±15 kV

## USB Serial Hardware

---

This section describes the characteristics of the USB serial hardware and the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

### Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

### Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

### CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息, 请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## One-Port USB Hardware

Dimensions.....	3.81 × 3.56 × 1.52 cm (1.5 × 1.4 × 0.6 in.)
Case material.....	PVC
Weight	
USB-232 .....	121 g (0.27 lb)
USB-485 .....	118 g (0.26 lb)
I/O connector.....	DB-9 male connector
USB connector .....	Captive cable with USB series A plug

Power requirement (from USB channel)

USB-485

+5 VDC .....175 mA typical  
500 mA maximum

USB-232

+5 VDC .....80 mA typical  
100 mA maximum

## Two and Four-Port USB Hardware

Dimensions .....21.08 × 12.45 × 3.56 cm  
(8.3 × 4.9 × 1.4 in.)

Case material .....Hard plastic with metal baseplate

Weight .....375 g (0.83 lb)

I/O connector .....DB-9 male connector

USB connector.....USB series B

Power requirement (from USB channel)

USB-485/2

+5 VDC .....300 mA typical  
500 mA maximum

USB-232/2

+5 VDC .....200 mA typical  
500 mA maximum

USB-232/4

+5 VDC .....300 mA typical  
500 mA maximum

Power requirement (from external supply)

USB-485/4 (9 V–30 V)

+12 VDC (typical).....225 mA typical  
500 mA maximum

# Environmental Characteristics

## Operating Environment

Ambient temperature..... 0 to 70 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 10 to 90%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

Altitude (maximum)..... 2,000 m

Indoor use only.

## Storage Environment

Ambient temperature

One port ..... –40 to 80 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Two and four port ..... –40 to 85 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity ..... 5 to 95%, noncondensing  
(Tested in accordance with  
IEC-60068-2-56.)

## Other Specifications

Maximum cable length

RS-485<sup>1</sup> ..... 30 m (limited by EMC/surge)

RS-232 ..... 2,500 pF equivalent  
(TIA-EIA-232-F 2.1.4)

Data line ESD protection (human body model)

RS-485 ..... ±15 kV

RS-232 ..... ±15 kV

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

# ENET Serial Hardware

---

This section describes the characteristics of the ENET serial hardware, along with the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

## Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 60950-1, EN 60950-1
- UL 60950-1, CSA 60950-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

## CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)



## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## Electrical Characteristics

Power requirement (from external supply)

External supply (9 V–30 V)

+12 VDC (typical) ..... 500 mA typical  
750 mA maximum

## Environmental Characteristics

### Operating Environment

Ambient temperature..... 0 to 70 °C  
(Tested in accordance with  
IEC-60068-2-1 and  
IEC-60068-2-2.)

Relative humidity .....	10 to 90%, noncondensing (Tested in accordance with IEC-60068-2-56.)
Altitude (maximum) .....	2,000 m

## Storage Environment

Ambient temperature .....	-40 to 85 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)
Relative humidity .....	5 to 95%, noncondensing (Tested in accordance with IEC-60068-2-56.)

## Physical Characteristics

Overall case size (dimensions) .....	21.0 × 12.4 × 3.7 cm (8.25 × 4.89 × 1.44 in.)
Case material .....	Hard plastic with metal baseplate
Weight .....	394 g (0.87 lb)
Serial connectors.....	DB-9 male connector

## Network Specifications

Ethernet connector .....	RJ-45
Connection type .....	IEEE 802.3 compliant 100Base-TX (100 Mbits/s) 10Base-T (10 Mbits/s)
Duplex mode.....	Half duplex

## Other Specifications

Maximum cable length	
RS-485 <sup>1</sup> .....	30 m (limited by EMC/surge)
RS-232 .....	2,500 pF equivalent (TIA-EIA-232-F 2.1.4)

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

Data line ESD protection (human body model)	
RS-485 .....	±15 kV
RS-232 .....	±15 kV

# ExpressCard Serial Hardware

---

This section describes the characteristics of the ExpressCard serial hardware, along with the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

## Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

## CE Compliance

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息, 请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## Hardware Specifications

Dimensions .....	34 × 75 × 5 mm (1.34 × 2.95 × 0.2 in.)
Weight	
NI ExpressCard-8420/2 .....	16 g (0.5 oz)
NI ExpressCard-8421/2 .....	17 g (0.6 oz)
Connectors	
I/O connector .....	26-position latching connector with 20 cm breakout cable to two DB-9 male connectors
ExpressCard .....	ExpressCard/34 standard connector interface

Power requirements  
(from ExpressCard USB interface)

Voltage.....	+3.3 VDC $\pm$ 10%
NI ExpressCard-8420/2	
+3.3 VDC.....	100 mA typical 250 mA maximum
NI ExpressCard-8421/2	
+3.3 VDC.....	160 mA typical 260 mA maximum

## Environmental Characteristics

Altitude (maximum)..... 2,000 m (at 25 °C ambient temperature)

Pollution Degree ..... 2

Indoor use only.

## Operating Environment

Ambient temperature..... 0 to 65 °C  
(Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)

Relative humidity ..... 5 to 95%, noncondensing  
(Tested in accordance with IEC-60068-2-56.)



**Hot Surface** Be careful when removing ExpressCards. Recently used ExpressCards may exceed safe handling temperatures.

## Storage Environment

Ambient temperature..... -20 to 65 °C  
(Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)

Nonoperating thermal shock ..... -20 to 65 °C, 5 shocks

## Other Specifications

Maximum cable length

RS-485 <sup>1</sup> .....	30 m (limited by EMC/surge)
RS-232 .....	2,500 pF equivalent (TIA-EIA-232-F 2.1.4)

Data line ESD protection (human body model)

RS-485 .....	±15 kV
RS-232 .....	±15 kV

## PCMCIA Serial Hardware

---

This section describes the characteristics of the PCMCIA serial hardware, along with the recommended operating conditions.



**Note** This equipment is intended for indoor use only.

## Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 60950-1, EN 60950-1
- UL 60950-1, CSA 60950-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326 (IEC 61326): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** For the standards applied to assess the EMC of this product, refer to the [Online Product Certification](#) section.



**Note** For EMC compliance, operate this device with shielded cabling.

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

# CE Compliance (€)

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *NI and the Environment* Web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit [ni.com/environment/weee](http://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

## Hardware Specifications

Dimensions.....	Type II PC card
I/O connector.....	Adapter cable with DB-9 male Dsub connector and converter for PC card

Power requirement (from PCMCIA expansion slot)

PCMCIA-232	
+5 VDC .....	40 mA typical 150 mA maximum
PCMCIA-485	
+5 VDC .....	110 mA typical 225 mA maximum
PCMCIA-232/2	
+5 VDC .....	60 mA typical 250 mA maximum
PCMCIA-485/2	
+5 VDC .....	150 mA typical 400 mA maximum
PCMCIA-232/4	
+5 VDC .....	60 mA typical 200 mA maximum

## Environmental Characteristics

### Operating Environment

Ambient temperature .....	0 to 55 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)
Relative humidity .....	10 to 90%, noncondensing (Tested in accordance with IEC-60068-2-56.)
Altitude (maximum) .....	2,000 m

### Storage Environment

Ambient temperature .....	-40 to 120 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2.)
Relative humidity .....	5 to 95%, noncondensing (Tested in accordance with IEC-60068-2-56.)



## Other Specifications

### Maximum cable length

RS-485 <sup>1</sup> .....	30 m (limited by EMC/surge)
RS-232 .....	2,500 pF equivalent (TIA-EIA-232-F 2.1.4)

### Data line ESD protection (human body model)

RS-485 .....	±15 kV
RS-232 .....	±15 kV

---

<sup>1</sup> RS-485 is capable of 1.2 km (4,000 ft) without surge limitation.

# Where to Go for Support

---

The National Instruments Web site is your complete resource for technical support. At [ni.com/support](http://ni.com/support) you have access to everything from troubleshooting and application development self-help resources to email and phone assistance from NI Application Engineers.

A Declaration of Conformity (DoC) is our claim of compliance with the Council of the European Communities using the manufacturer's declaration of conformity. This system affords the user protection for electromagnetic compatibility (EMC) and product safety. You can obtain the DoC for your product by visiting [ni.com/certification](http://ni.com/certification). If your product supports calibration, you can obtain the calibration certificate for your product at [ni.com/calibration](http://ni.com/calibration).

National Instruments corporate headquarters is located at 11500 North Mopac Expressway, Austin, Texas, 78759-3504. National Instruments also has offices located around the world to help address your support needs. For telephone support in the United States, create your service request at [ni.com/support](http://ni.com/support) and follow the calling instructions or dial 512 795 8248. For telephone support outside the United States, contact your local branch office:

Australia 1800 300 800, Austria 43 662 457990-0,  
Belgium 32 (0) 2 757 0020, Brazil 55 11 3262 3599,  
Canada 800 433 3488, China 86 21 5050 9800,  
Czech Republic 420 224 235 774, Denmark 45 45 76 26 00,  
Finland 358 (0) 9 725 72511, France 01 57 66 24 24,  
Germany 49 89 7413130, India 91 80 41190000, Israel 972 3 6393737,  
Italy 39 02 41309277, Japan 0120-527196, Korea 82 02 3451 3400,  
Lebanon 961 (0) 1 33 28 28, Malaysia 1800 887710,  
Mexico 01 800 010 0793, Netherlands 31 (0) 348 433 466,  
New Zealand 0800 553 322, Norway 47 (0) 66 90 76 60,  
Poland 48 22 328 90 10, Portugal 351 210 311 210,  
Russia 7 495 783 6851, Singapore 1800 226 5886,  
Slovenia 386 3 425 42 00, South Africa 27 0 11 805 8197,  
Spain 34 91 640 0085, Sweden 46 (0) 8 587 895 00,  
Switzerland 41 56 2005151, Taiwan 886 02 2377 2222,  
Thailand 662 278 6777, Turkey 90 212 279 3031,  
United Kingdom 44 (0) 1635 523545

National Instruments, NI, [ni.com](http://ni.com), and LabVIEW are trademarks of National Instruments Corporation. Refer to the *Terms of Use* section on [ni.com/legal](http://ni.com/legal) for more information about National Instruments trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering National Instruments products/technology, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your media, or the *National Instruments Patent Notice* at [ni.com/patents](http://ni.com/patents).