

# NI PXI-2532 Specifications

## 512-Crosspoint, 1-Wire Matrix

This document lists specifications for the National Instruments PXI-2532 512-crosspoint, 1-wire matrix. All specifications are subject to change without notice. Visit [ni.com/manuals](http://ni.com/manuals) for the most current specifications.

Configurations ..... 4 × 128, 1-wire matrix; 8 × 64, 1-wire matrix; 4 × 64, 2-wire matrix; 8 × 32, 2-wire matrix;  
Dual 4 × 64, 1-wire matrix; Dual 8 × 32, 1-wire matrix

### Input Characteristics

All input characteristics are DC, AC<sub>pk</sub>, or a combination unless otherwise specified.

Maximum switching voltage

Channel-to-channel ..... 100 V  
Channel-to-ground..... 100 V, CAT I



**Caution** This module is rated for Measurement Category I and intended to carry signal voltages no greater than 100 V. This module can withstand up to 500 V impulse voltage. Do *not* use this module for connection to signals or for measurements within Categories II, III, or IV. Do *not* connect to MAINS supply circuits (for example, wall outlets) of 115 or 230 VAC. Refer to the *Read Me First: Safety and Radio-Frequency Interference* document for more information on measurement categories.

When hazardous voltages (>42.4 V<sub>pk</sub>/60 VDC) are present on any relay terminal, safety low-voltage (<42.4 V<sub>pk</sub>/60 VDC) cannot be connected to any other relay terminal.

Maximum current ..... 0.5 A  
(switching or carry, per channel)

Maximum switching power ..... 10 W  
(per channel)

DC path resistance

Initial ..... <1 Ω  
End of life ..... ≥2 Ω  
Open channel ..... >10<sup>9</sup> Ω



**Note** DC path resistance typically remains low for the life of the relay. At the end of relay life, the path resistance rapidly rises above 2 Ω. Load ratings apply to relays used within the specification before the end of relay life.

Thermal EMF

1-wire ..... <50 μV  
2-wire ..... <20 μV

Bandwidth (-3 dB, 50 Ω termination)

1-wire row/column ..... ≥30 MHz  
2-wire row/column ..... ≥25 MHz

Crosstalk (50 Ω termination)

Channel-to-channel  
10 kHz ..... <-89 dB  
100 kHz ..... <-73 dB  
1 MHz ..... <-54 dB  
10 MHz ..... <-36 dB

Isolation (50 Ω termination)

Open channel  
10 kHz ..... >91 dB  
100 kHz ..... >71 dB  
1 MHz ..... >51 dB  
10 MHz ..... >32 dB

### Dynamic Characteristics

Maximum cycle speed ..... 2,000 cycles/s

Simultaneous drive limit ..... 40 relays

Relay operate time ..... 0.25 ms

Release time ..... 0.25 ms

Expected relay life	
Mechanical .....	10 <sup>9</sup> cycles
Electrical (resistive)	
10 V, 100 mA .....	10 <sup>7</sup> cycles
20 V, 500 mA .....	5 × 10 <sup>6</sup> cycles
100 V, 10 mA .....	5 × 10 <sup>5</sup> cycles



**Note** Optional series protection resistance, available for the terminal blocks, increases the expected relay life at higher voltages. This series protection resistance shields the reed relays from the effects of cable and load capacitance. For more information, refer to the *Reed Relay Protection* tutorial at [ni.com/zone](http://ni.com/zone).

## Trigger Characteristics

### Input trigger

Sources .....	PXI trigger lines 0–7
Minimum pulse width .....	150 ns



**Note** The NI PXI-2532 can recognize trigger pulse widths <150 ns if you disable digital filtering. For information about disabling digital filtering, refer to the *NI Switches Help* at [ni.com/manuals](http://ni.com/manuals).

### Output trigger

Destinations .....	PXI trigger lines 0–7
Pulse width .....	Programmable (1 μs to 62 μs)

## Physical Characteristics

Relay type.....Reed



**Note** NI advises against installing reed relay modules directly adjacent to an embedded controller with a magnetic hard drive because of the sensitivity of reed relays and the possibility of interference from magnetic hard drives,

Relay contact material.....Rhodium

I/O connectors .....2, 160 pos,  
Samtec BTE-EM series



**Note** Terminal block connectivity is with standard 0.050 inch pitch headers. Refer to the *Accessories* section for more information.

PXI power requirement.....	10 W at 5 V 2 W at 3.3 V
Dimensions (W × H × D).....	Single PXI slot, 3U 2 cm × 10 cm × 17.5 cm (0.8 in. × 3.9 in. × 6.9 in.)
Weight.....	454 g (1 lb)

## Environment

The NI PXI-2532 is intended for indoor use only.

Operating temperature .....	0 °C to 55 °C
Storage temperature .....	–20 °C to 70 °C
Relative humidity.....	5% to 85%, noncondensing
Pollution Degree .....	2

Approved at altitudes up to 2,000 m.

## Shock and Vibration

Operational shock .....	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC-60068-2-27. Test profile developed in accordance with MIL-PRF-28800F.)
-------------------------	---

### Random vibration

Operating .....	5 to 500 Hz, 0.3 g <sub>rms</sub>
Nonoperating .....	5 to 500 Hz, 2.4 g <sub>rms</sub> (Tested in accordance with IEC-60068-2-64. Nonoperating test profile exceeds the requirements of MIL-PRF-28800F, Class 3.)

## Accessories

Visit [ni.com](http://ni.com) for more information about the following accessories.



**Note** The specifications listed in this document, including the safety and compliance certifications, also apply to the NI PXI-2532 terminal blocks unless otherwise noted in the terminal block installation instructions.

**Table 1.** NI Accessories for the NI PXI-2532

Accessory	Part Number
NI TB-2640 terminal block (4 × 128, 1-wire matrix)	779056-01
NI TB-2640 terminal block, with protection resistance	779056-02
NI TB-2641 terminal block (8 × 64, 1-wire matrix)	779056-03
NI TB-2641 terminal block, with protection resistance	779056-04
NI TB-2643 terminal block (4 × 64, 2-wire matrix or dual 4 × 64, 1-wire matrix)	779056-07
NI TB-2643 terminal block, with protection resistance	779056-08
NI TB-2644 terminal block (8 × 32, 2-wire matrix or dual 8 × 32, 1-wire matrix)	779056-09
NI TB-2644 terminal block, with protection resistance	779056-10




**Note** Refer to the terminal block installation instructions for signal connectivity and matrix expansion options. Contact NI for custom terminal block designs.



**Caution** You *must* install mating connectors according to local safety codes and standards and according to the specifications provided by the connector manufacturer. You are responsible for verifying safety compliance of third-party connectors and their usage according to the relevant standard(s), including UL and CSA in North America and IEC and VDE in Europe.

**Table 2.** Third-Party Accessory for the NI PXI-2532

Accessory	Manufacturer	Manufacturer Part Number
Module mating connector	Samtec	BSE-080-01-L-D-A



**Figure 1.** NI PXI-2532 Configuration (Relay Shown in Power-On State)




Figure 2. NI PXI-2532 Pinouts



**Caution** Low voltage pins are reserved for future use. These pins should remain disconnected and isolated from row and column channels when high voltage is present.

# Compliance and Certifications

## Safety

This product is designed to meet the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1
- CAN/CSA-C22.2 No. 61010-1



**Note** For UL and other safety certifications, refer to the product label or visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Electromagnetic Compatibility

Emissions.....	EN 55011 Class A at 10 m FCC Part 15A above 1 GHz
Immunity.....	EN 61326:1997 + A2:2001, Table 1
EMC/EMI.....	CE, C-Tick, and FCC Part 15 (Class A) Compliant



**Note** For EMC compliance, operate this device with shielded cabling.

## CE Compliance

This product meets the essential requirements of applicable European Directives, as amended for CE marking, as follows:

Low-Voltage Directive (safety).....	73/23/EEC
Electromagnetic Compatibility Directive (EMC).....	89/336/EEC



**Note** Refer to the Declaration of Conformity (DoC) for this product for any additional regulatory compliance information. To obtain the DoC for this product, visit [ni.com/certification](http://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

National Instruments, NI, ni.com, and LabVIEW are trademarks of National Instruments Corporation. Refer to the *Terms of Use* section on [ni.com/legal](http://ni.com/legal) for more information about National Instruments trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering National Instruments products, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your CD, or [ni.com/patents](http://ni.com/patents).