

SPECIFICATIONS

USRP-2950

50 MHz to 2.2 GHz Tunable RF Transceiver

These specifications apply to the USRP-2950 40 MHz Software Defined Radio Device and the USRP-2950 120 MHz Software Defined Radio Device. When not otherwise specified, the specifications for the USRP-2950 in this document refer to both the USRP-2950 40 MHz and the USRP-2950 120 MHz. The USRP-2950 contains a GPS-disciplined oscillator (GPSDO), which enables you to lock the internal clocks to a GPS reference signal, synchronize using GPS timing information, and query GPS location information.

Contents

Definitions.....	1
Conditions.....	2
Transmitter.....	2
Receiver.....	2
Power.....	3
Onboard DRAM.....	3
Physical Characteristics.....	3
Environment.....	4
Operating Environment.....	4
Compliance and Certifications.....	4
Safety.....	4
Electromagnetic Compatibility.....	4
CE Compliance.....	5
Online Product Certification.....	5
Environmental Management.....	5

Definitions

Warranted specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

Characteristics describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- *Typical* specifications describe the expected performance met by a majority of the models.
- *Nominal* specifications describe parameters and attributes that may be useful in operation.

Specifications are *Characteristics* unless otherwise noted.

Conditions

Specifications are valid at 25 °C unless otherwise noted.

Transmitter

Number of channels	2
Frequency range	50 MHz to 2.2 GHz
Frequency step	<1 kHz
Maximum output power (P_{out})	
50 MHz to 1.2 GHz	50 mW to 100 mW (17 dBm to 20 dBm)
1.2 GHz to 2.2 GHz	30 mW to 70 mW (15 dBm to 18 dBm)
Gain range ¹	0 dB to 31 dB
Gain step	1.0 dB
Maximum instantaneous real-time bandwidth	
USRP-2950 40 MHz	40 MHz
USRP-2950 120 MHz	120 MHz
Maximum I/Q sample rate	200 MS/s
Digital-to-analog converter (DAC)	
Resolution	16 bit
Spurious-free dynamic range (sFDR)	80 dB

Receiver

Number of channels	2
Frequency range	50 MHz to 2.2 GHz
Frequency step	<1 kHz
Gain range ²	0 dB to 37.5 dB
Gain step	0.5 dB
Maximum input power (P_{in})	-15 dBm
Noise figure	5 dB to 7 dB

¹ The output power resulting from the gain setting varies over the frequency band and among devices.

² The received signal amplitude resulting from the gain setting varies over the frequency band and among devices.

Maximum instantaneous real-time bandwidth

USRP-2950 40 MHz	40 MHz
USRP-2950 120 MHz	120 MHz
Maximum I/Q sample rate	200 MS/s
Analog-to-digital converter (ADC)	
Resolution	14 bit
sFDR	88 dB

Power



Caution The protection provided by this product may be impaired if it is used in a manner not described in this document.

Input voltage	9 V to 16 V, DC
Input current	7.5 A, maximum
Typical power consumption	38 W to 44 W, varies by application



Caution You must use an LPS or Class 2 power supply with the USRP-2950. The power supply must also meet any safety and compliance requirements for the country of use.

Onboard DRAM

Memory size	1,024 MB
-------------	----------

Physical Characteristics

If you need to clean the module, wipe it with a dry towel.

Physical dimensions

(L × W × H)	26.67 cm × 4.06 cm × 21.84 cm (10.5 in. × 1.6 in. × 8.6 in.)
Weight	1.588 kg (3.50 lb)

Environment

Maximum altitude	2,000 m (800 mbar) (at 25 °C ambient temperature)
------------------	---

Pollution Degree	2
------------------	---

Indoor use only.

Operating Environment

Operating temperature	23 °C ± 5 °C
-----------------------	--------------

Relative humidity range	10% to 90%, noncondensing (tested in accordance with IEC 60068-2-56)
-------------------------	--

Compliance and Certifications

Safety

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1



Note For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- EN 55022 (CISPR 22): Class A emissions
- EN 55024 (CISPR 24): Immunity
- AS/NZS CISPR 11: Group 1, Class A emissions
- AS/NZS CISPR 22: Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia, and New Zealand (per CISPR 11), Class A equipment is intended for use only in heavy-industrial locations.



Note Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note For EMC declarations, certifications, and additional information, refer to the [Online Product Certification](#) section.

CE Compliance

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)

Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *Minimize Our Environmental Impact* web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

Waste Electrical and Electronic Equipment (WEEE)



EU Customers At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法（中国 RoHS）



中国客户 National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)

Information is subject to change without notice. Refer to the *NI Trademarks and Logo Guidelines* at ni.com/trademarks for information on NI trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering NI products/technology, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your media, or the *National Instruments Patent Notice* at ni.com/patents. You can find information about end-user license agreements (EULAs) and third-party legal notices in the `readme` file for your NI product. Refer to the *Export Compliance Information* at ni.com/legal/export-compliance for the NI global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data. NI MAKES NO EXPRESS OR IMPLIED WARRANTIES AS TO THE ACCURACY OF THE INFORMATION CONTAINED HEREIN AND SHALL NOT BE LIABLE FOR ANY ERRORS. U.S. Government Customers: The data contained in this manual was developed at private expense and is subject to the applicable limited rights and restricted data rights as set forth in FAR 52.227-14, DFAR 252.227-7014, and DFAR 252.227-7015.

© 2014—2017 National Instruments. All rights reserved.

374194D-01 July 13, 2017