

NI PXI-2548 Specifications

2.7 GHz Quad SPDT Relay Module

このドキュメントには、日本語ページも含まれています。

This document lists specifications for the NI PXI-2548 relay module. All specifications are subject to change without notice. Visit ni.com/manuals for the most current specifications.

Topology Quad SPDT

Refer to the *NI Switches Help* for detailed topology and front panel connector information.

Typical values are representative of an average module operating at room temperature (25 °C).

Input Characteristics

All input characteristics are DC, AC_{rms} , or a combination unless otherwise specified.

Maximum switching voltage 30 V

Maximum switching current 0.5 A
(per channel)

Maximum carry current 0.5 A
(per channel)

Maximum RF power 10 W



Caution The switching power is limited by the maximum switching current and the maximum voltage. Switching power must not exceed 10 W per channel.



Note National Instruments recommends against switching active RF signals. As a relay actuates, the channel is momentarily unterminated. Some RF sources can be damaged by reflections if their outputs are not properly terminated. Refer to your RF source documentation for more information.

Typical DC path resistance

Initial <0.25 Ω

End-of-life $\geq 1.0 \Omega$

Path resistance is a combination of relay contact resistance and trace resistance. Contact resistance typically remains low for the life of a relay. At the end of relay life, the contact resistance rises rapidly above 1.0 Ω .

RF Performance Characteristics

Characteristic impedance (Z_0) 50 Ω nominal

Values in parentheses are typical.

Insertion loss

≤ 1.5 GHz <0.7 dB (<0.4 dB)

≤ 2.7 GHz <0.9 dB (<0.6 dB)

Voltage standing wave ratio (VSWR)

≤ 1.5 GHz <1.25 (<1.15)

≤ 2.7 GHz <1.5 (<1.35)

Typical isolation

≤ 1.5 GHz >58 dB

≤ 2.7 GHz >39 dB

Typical crosstalk

≤ 1.5 GHz <-60 dB

≤ 2.7 GHz <-45 dB

Typical channel-to-channel skew <15 ps

Typical propagation delay 710 ps

Typical rise time (10% to 90%) 55 ps

Refer to Figures 1, 2, and 3 for typical insertion loss, typical VSWR, and typical isolation, respectively.




Figure 1. Typical Insertion Loss




Figure 2. Typical VSWR




Figure 3. Typical Isolation

Dynamic Characteristics

Maximum relay operate time..... 10.4 ms



Note Certain applications may require additional time for proper settling. For information about including additional settling time, refer to the *NI Switches Help*.

Maximum scan rate..... 45 channels/s

Expected relay life

Mechanical 1×10^6 cycles

Electrical..... 3×10^5 cycles
(30 V, 10 mA, DC resistive)

Trigger Characteristics

Input trigger

Sources PXI trigger lines 0–7

Minimum pulse width..... 150 ns



Note The NI PXI-2548 can recognize trigger pulse widths less than 150 ns by disabling digital filtering. For information about disabling digital filtering, refer to the *NI Switches Help*.

Output trigger

Destinations PXI trigger lines 0–7

Pulse width Programmable
(1 μ s to 62 μ s)

Physical Characteristics

Relay type Electromechanical,
latching

I/O connectors..... 12 SMA jacks,
gold plated

PXI power requirement..... 3.7 W at 5 V,
0.3 W at 3.3 V

Dimensions (L \times W \times H) 3U, one slot,
PXI/cPCI module
21.6 \times 2.0 \times 13.0 cm
(8.5 \times 0.8 \times 5.1 in.)

Weight..... 255 g (9 oz)

Environment

Operating temperature	0 °C to 55 °C
Storage temperature	-20 °C to 70 °C
Relative humidity	5% to 85%, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m
Indoor use only.	

Shock and Vibration

Operational Shock.....	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC-60068-2-27. Test profile developed in accordance with MIL-PRF-28800F.)
Random Vibration	
Operating	5 to 500 Hz, 0.3 g _{rms}
Nonoperating	5 to 500 Hz, 2.4 g _{rms} (Tested in accordance with IEC-60068-2-64. Nonoperating test profile exceeds the requirements of MIL-PRF-28800F, Class 3.)

Accessories

Visit ni.com for more information about the following accessories.

Table 1. NI Accessories for the NI PXI-2548

Accessory	Length	Part Number
SMA 100, SMA male to SMA male flexible cable	0.15 m	763443-01
	0.45 m	763444-01
MCX plug to SMA plug	0.3 m	188377-0R3
	1.0 m	188377-01
SMA 50 Ohm termination plug	—	778353-01
Torque wrench for SMA connectors	—	187106-01
SMA plug (female) to SMB jack (male) adapter	—	779674-01

Figure 4 shows the NI PXI-2548 power-on state.




Figure 4. NI PXI-2548 Power-On State

Compliance and Certifications

Safety

This product is designed to meet the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



Note For UL and other safety certifications, refer to the product label or visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Electromagnetic Compatibility

This product is designed to meet the requirements of the following standards of EMC for electrical equipment for measurement, control, and laboratory use:

- EN 61326 EMC requirements; Minimum Immunity
- EN 55011 Emissions; Group 1, Class A
- CE, C-Tick, ICES, and FCC Part 15 Emissions; Class A



Note For EMC compliance, operate this device with shielded cabling.



Caution Device relays might change state momentarily during electrostatic discharge.

CE Compliance

This product meets the essential requirements of applicable European Directives, as amended for CE marking, as follows:

- 73/23/EEC; Low-Voltage Directive (safety)
- 89/336/EEC; Electromagnetic Compatibility Directive (EMC)



Note Refer to the Declaration of Conformity (DoC) for this product for any additional regulatory compliance information. To obtain the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Waste Electrical and Electronic Equipment (WEEE)



EU Customers At the end of their life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers and National Instruments WEEE initiatives, visit ni.com/environment/weee.htm.

NI PXI-2548 仕様

2.7 GHz 4 バンク SPDT リレーモジュール

このドキュメントには、NI PXI-2548 リレーモジュールの仕様が記載されています。以下の仕様は事前の通知なしに変更されることがあります。最新の仕様については、ni.com/manuals を参照してください。

トポロジ 4 バンク SPDT

トポロジとフロントパネルコネクタについては、『NI スイッチヘルプ』を参照してください。

標準値は、室温（25 °C）で動作の平均単位を表しています。

入力特性

すべての入力特性は特に注釈のない限り、DC、 AC_{rms} 、またはその組み合わせです。

最大スイッチ電圧 30 V

最大スイッチ電流 0.5 A
(チャンネルあたり)

最大許容電流 0.5 A
(チャンネルあたり)

最大 RF 電力 10 W



注意 スイッチ電力は最大スイッチ電流および最大電圧により制限されます。スイッチ電力はチャンネルあたり 10 W 未満である必要があります。



メモ ナショナルインスツルメンツは動作中の RF 信号を切り替えることは推奨しません。リレーが作動すると、チャンネルは一時的に終端されない状態となります。RF 信号源によっては、出力が正しく終端されないで反射によって損傷する場合があります。詳細については、RF 信号源の関連ドキュメントを参照してください。

標準 DC パス抵抗

初期 <0.25 Ω

寿命末期 $\geq 1.0 \Omega$

パス抵抗は、リレー接触抵抗およびトレース抵抗の組み合わせです。通常、リレー寿命の有効期間中、接触抵抗は低レベルに抑えられます。リレーの寿命末期時には、パスの抵抗は急速に大きくなり、 1.0Ω 以上になります。

RF 性能特性

特性インピーダンス (Z_0) 50 Ω 公称

括弧内の値は標準値です。

挿入損失

≤ 1.5 GHz <0.7 dB (<0.4 dB)

≤ 2.7 GHz <0.9 dB (<0.6 dB)

電圧定在波比 (VSWR)

≤ 1.5 GHz <1.25 (<1.15)

≤ 2.7 GHz <1.5 (<1.35)

標準絶縁

≤ 1.5 GHz >58 dB

≤ 2.7 GHz >39 dB

標準クロストーク

≤ 1.5 GHz <-60 dB

≤ 2.7 GHz <-45 dB

標準チャンネル間スキュー <15 ps

標準伝播遅延 710 ps

標準立ち上がり時間

(10 ~ 90%) 55 ps

挿入損失、VSWR、および絶縁の各標準値については、図1、2、および3を参照してください。




図1 標準挿入損失




図2 標準 VSWR




図3 標準絶縁

動特性

最大リレー動作時間 10.4 ms



メモ アプリケーションによっては、適切な整定が行われるために、追加の整定時間を必要とします。整定時間の追加についての情報は、『NI スイッチヘルプ』を参照してください。

最大スキャンレート 45 チャンネル / s

リレー寿命

機械的 1×10^6 サイクル

電氣的 3×10^5 サイクル
(30 V、10 mA、DC 抵抗)

トリガ特性

入カトリガ

入力元 PXI トリガライン
0 ~ 7

最小パルス幅 150 ns



メモ NI PXI-2548 は、デジタルフィルタを無効にすることによって、150 ns 未満のトリガパルス幅を認識することができます。デジタルフィルタを無効にする方法の詳細については、『NI スイッチヘルプ』を参照してください。

出カトリガ

出力先 PXI トリガライン
0 ~ 7

パルス幅 プログラム可能
(1 ~ 62 μ s)

物理特性

リレータイプ メカニカル、ラッチ型

I/O コネクタ 12 SMA ジャック、
金メッキ

PXI 所要電力 5 V 時 3.7 W、
3.3 V 時 0.3 W

外形寸法 (奥行 × 幅 × 高さ) 3U、1 スロット、
PXI/cPCI モジュール、
21.6 × 2.0 × 13.0 cm
(8.5 × 0.8 × 5.1 in.)

重量 255 g (9 oz)

環境

動作温度	0 ~ 55 °C
保管温度	-20 ~ 70 °C
相対湿度	5 ~ 85 % (結露なきこと)
汚染度	2
最大使用高度	2,000 m
室内使用のみ。	

耐衝撃 / 振動

動作時衝撃	最大 30 g、半正弦波、 11 ms パルス (IEC-60068-2-27 に準 拠して試験、 MIL-PRF-28800F に準 拠してテストプロファ イルを確立)
-------------	---

ランダム振動

動作時	5 ~ 500 Hz、0.3 g _{rms}
非動作時	5 ~ 500 Hz、2.4 g _{rms} (IEC-60068-2-64 に準 拠して試験。非動作時 のテストプロファイル は MIL-PRF-28800F、 Class 3 の要件以上)

アクセサリ

以下のアクセサリの詳細については、ni.com/jp を参照してください。

表 1 NI PXI-2548 対応の NI アクセサリ

アクセサリ	長さ	製品番号
SMA 100、SMA オス⇔ SMA オスフレキシブル ケーブル	0.15 m	763443-01
	0.45 m	763444-01
MCX ⇔ SMA プラグ	0.3 m	188377-0R3
	1.0 m	188377-01
SMA 50 Ω 終端プラグ	—	778353-01
SMA コネクタ用トルクレ ンチ	—	187106-01
SMA プラグ (メス) ⇔ SMB ジャック (オス) アダプタ	—	779674-01

図 4 は、電源投入状態の NI PXI-2548 を示しています。




図 4 NI PXI-2548 電源投入時の状態

認可および準拠

安全性

この製品は、計測、制御、実験に使用される電気装置に関する以下の安全規格の必要条件を満たすように設計されています。

- IEC 61010-1、EN 61010-1
- UL 61010-1、CSA 61010-1



メモ UL および他の安全保証については、製品のラベルを参照するか、ni.com/certification (英語) にアクセスしてモデル番号または製品ラインで検索し、保証の欄の該当するリンクをクリックしてください。

電磁両立性

この製品は、計測、制御、実験に使用される電気装置に関する以下の EMC 規格の必要条件を満たすように設計されています。

- EN 61326 EMC 必要条件、最小イミュニティ
- EN 55011 エミッション (Group 1, Class A)
- CE、C-Tick、ICES、FCC Part 15 エミッション : Class A



メモ EMC に適合させるには、このデバイスをシールドケーブルと一緒に使用してください。



注意 デバイスリレーは、静電放電時に状態が一瞬変化する場合があります。

CE 適合

この製品は、以下のように、CE マーク改正に基づいて、該当する EC 理事会指令による基本的要件に適合しています。

- 73/23/EEC、低電圧指令 (安全性)
- 89/336/EEC、電磁両立性指令 (EMC)



メモ この製品のこのほかの適合規格については、この製品の適合宣言 (DoC) を参照してください。この製品の適合宣言を入手するには、ni.com/certification (英語) にアクセスして型番または製品ラインで検索し、保証の欄の該当するリンクをクリックしてください。

廃電気電子機器 (WEEE)



欧州のお客様へ 製品寿命を過ぎたすべての製品は、必ず WEEE リサイクルセンターへ送付してください。WEEE リサイクルセンターおよびナショナルインスツルメンツの WEEE への対応に関する詳細は、ni.com/environment/weee.htm (英語) を参照してください。