

SPECIFICATIONS

NI PXIe-7847R

R Series Reconfigurable I/O Module (AI, AO, DIO) for PXI Express, 8 AI, 8 AO, 48 DIO, 500 kS/s AI, 512 MB DRAM, Kintex-7 160T FPGA

This document contains the specifications for the NI PXIe-7847R. Specifications are typical at 25 °C unless otherwise noted.



Caution Using the NI PXIe-7847R in a manner not described in this document may impair the protection the NI PXIe-7847R provides.

Analog Input

Number of channels	8
Input modes (software-selectable; selection applies to all channels)	DIFF, NRSE, RSE
Type of ADC	Successive approximation register (SAR)
Resolution	16 bits
Conversion time	2 μ s
Maximum sampling rate (per channel)	500 kS/s
Input impedance	
Powered on	1.25 G Ω 2 pF
Powered off/overload	4 k Ω minimum
Input signal range (software-selectable)	± 1 V, ± 2 V, ± 5 V, ± 10 V
Input bias current	± 5 nA
Input offset current	± 5 nA
Input coupling	DC
Overvoltage protection	
Powered on	± 42 V maximum
Powered off	± 35 V maximum

Table 1. AI Operating Voltage Ranges Over Temperature

Range (V)	Measurement Voltage, AI+ to AI-			Maximum Working Voltage (Signal + Common Mode)
	Minimum (V) ¹	Typical (V)	Maximum (V)	
±10	±10.37	±10.5	±10.63	±12 V of ground
±5	±5.18	± 5.25	±5.32	±10 V of ground
±2	±2.07	±2.1	±2.13	±8.5 V of ground
±1	±1.03	±1.05	±1.06	±8 V of ground

AI Absolute Accuracy

Absolute accuracy at full scale numbers is valid immediately following internal calibration and assumes the device is operating within 10 °C of the last external calibration. Accuracies listed are valid for up to one year from the device external calibration.

Absolute accuracy at full scale on the analog input channels is determined using the following assumptions:

- TempChangeFromLastExternalCal = 10 °C
- TempChangeFromLastInternalCal = 1 °C
- number_of_readings = 10,000
- CoverageFactor = 3 σ

Table 2. AI Absolute Accuracy (Calibrated)

Specifications	Range			
	±10 V	±5 V	±2 V	±1 V
Residual Gain Error (ppm of Reading)	104.4	105.9	110.6	118.4
Gain Tempco (ppm/°C)	20	20	20	20
Reference Tempco (ppm/°C)	4	4	4	4
Residual Offset Error (ppm of Range)	16.4	16.4	16.4	16.4
Offset Tempco (ppm of Range/°C)	4.18	4.17	4.41	4.63
INL Error (ppm of range)	42.52	46.52	46.52	50.52

¹ The minimum measurement voltage range is the largest voltage the NI PXIe-7847R is guaranteed to accurately measure.

Table 2. AI Absolute Accuracy (Calibrated) (Continued)

Specifications	Range			
	±10 V	±5 V	±2 V	±1 V
Random Noise, σ (μVrms)	263	156	90	74
Absolute Accuracy at Full Scale (μV)	2,283	1,170	479	252

Table 3. AI Absolute Accuracy (Uncalibrated)

Specifications	Range			
	±10 V	±5 V	±2 V	±1 V
Residual Gain Error (ppm of Reading)	2,921	3,021	3,021	3,021
Gain Tempco (ppm/°C)	20	20	20	20
Reference Tempco (ppm/°C)	4	4	4	4
Residual Offset Error (ppm of Range)	661	671	700	631
Offset Tempco (ppm of Range/°C)	4.18	4.17	4.41	4.63
INL Error (ppm of range)	42.52	46.52	46.52	50.52
Random Noise, σ (μVrms)	263	156	90	74
Absolute Accuracy at Full Scale (μV)	36,895	19,018	7,667	3,769

Calculating Absolute Accuracy

$$\text{AbsoluteAccuracy} = \text{Reading} \times (\text{GainError}) + \text{Range} \times (\text{OffsetError}) + \text{NoiseUncertainty}$$

$$\text{GainError} = \text{ResidualGainError} + \text{GainTempco} \times (\text{TempChangeFromLastInternalCal}) + \text{ReferenceTempco} \times (\text{TempChangeFromLastExternalCal})$$

$$\text{OffsetError} = \text{ResidualOffsetError} + \text{OffsetTempco} \times (\text{TempChangeFromLastInternalCal}) + \text{INL_Error}$$

$$\text{NoiseUncertainty} = \frac{\text{RandomNoise} \times \text{CoverageFactor}}{\sqrt{\text{number_of_readings}}}$$

Refer to the following equation for an example of calculating absolute accuracy.

Absolute accuracy at full scale on the analog input channels is determined using the following assumptions:

- $\text{TempChangeFromLastExternalCal} = 10\text{ }^{\circ}\text{C}$
- $\text{TempChangeFromLastInternalCal} = 1\text{ }^{\circ}\text{C}$
- $\text{number_of_readings} = 10,000$
- $\text{CoverageFactor} = 3\sigma$

$$\text{GainError} = 104.4\text{ ppm} + 20\text{ ppm} \times 1 + 4\text{ ppm} \times 10$$

$$\text{GainError} = 164.4\text{ ppm}$$

$$\text{OffsetError} = 16.4\text{ ppm} + 4.18\text{ ppm} \times 1 + 42.52\text{ ppm}$$

$$\text{OffsetError} = 63.1\text{ ppm}$$

$$\text{NoiseUncertainty} = \frac{263\text{ }\mu\text{V} \times 3}{\sqrt{10,000}}$$

$$\text{NoiseUncertainty} = 7.89\text{ }\mu\text{V}$$

$$\text{AbsoluteAccuracy} = 10\text{ V} \times (\text{GainError}) + 10\text{ V} \times (\text{OffsetError}) + \text{NoiseUncertainty}$$

$$\text{AbsoluteAccuracy} = 2,283\text{ }\mu\text{V}$$

DC Transfer Characteristics

INL	Refer to the AI Accuracy Table
DNL	± 0.4 LSB typical, ± 0.9 LSB maximum
No missing codes	16 bits guaranteed
CMRR, DC to 60 Hz	-100 dB

Dynamic Characteristics

Bandwidth

Small signal	1 MHz
Large signal	500 kHz

Table 4. Settling Time

Range (V)	Step Size (V)	Accuracy		
		±16 LSB	±4 LSB	±2 LSB
±10	±20.0	1.50 μs	4.00 μs	7.00 μs
	±2.0	0.50 μs	0.50 μs	1.00 μs
	±0.2	0.50 μs	0.50 μs	0.50 μs
±5	±10	1.50 μs	3.50 μs	7.50 μs
	±1	0.50 μs	0.50 μs	1.00 μs
	±0.1	0.50 μs	0.50 μs	0.50 μs
±2	±4	1.00 μs	3.50 μs	8.00 μs
	±0.4	0.50 μs	0.50 μs	1.00 μs
	±0.04	0.50 μs	0.50 μs	0.50 μs
±1	±2	1.00 μs	3.50 μs	12.00 μs
	±0.2	0.50 μs	0.50 μs	2.00 μs
	±0.02	0.50 μs	0.50 μs	0.50 μs

Crosstalk -80 dB, DC to 100 kHz, at 50 Ω

Analog Output

Output type	Single-ended, voltage output
Number of channels	8
Resolution	16 bits
Update time	1 μs
Maximum update rate	1 MS/s
Type of DAC	Enhanced R-2R

Range	±10 V
Output coupling	DC
Output impedance	0.5 Ω
Current drive	±2.5 mA
Protection	Short circuit to ground
Overvoltage protection	
Powered on	±15 V maximum
Powered off	±10 V maximum
Power-on state	User-configurable
Power-on glitch	1 V for 1 μs

Table 5. AO Operating Voltage Ranges for Over Temperature

Range (V)	Measurement Voltage, AO+ to AO GND		
	Minimum (V) ²	Typical (V)	Maximum (V)
±10	±10.1	±10.16	±10.22

AO Absolute Accuracy

Absolute accuracy at full scale numbers is valid immediately following internal calibration and assumes the device is operating within 10 °C of the last external calibration. Accuracies listed are valid for up to one year from the device external calibration.

Absolute accuracy at full scale on the analog output channels is determined using the following assumptions:

- TempChangeFromLastExternalCal = 10 °C
- TempChangeFromLastInternalCal = 1 °C

Table 6. AO Absolute Accuracy (Calibrated)

Specifications	±10 V Range
Residual Gain Error (ppm of Reading)	87.3
Gain Tempco (ppm/°C)	12.6
Reference Tempco (ppm/°C)	4
Residual Offset Error (ppm of Range)	41.1

² The minimum measurement voltage range is the largest voltage the NI PXIe-7847R is guaranteed to accurately measure.

Table 6. AO Absolute Accuracy (Calibrated) (Continued)

Specifications	±10 V Range
Offset Tempco (ppm of Range/°C)	7.8
INL Error (ppm of range)	61
Absolute Accuracy at Full Scale (μV)	2,498

Table 7. AO Absolute Accuracy (Uncalibrated)

Specifications	±10 V Range
Residual Gain Error (ppm of Reading)	2,968.6
Gain Tempco (ppm/°C)	12.6
Reference Tempco (ppm/°C)	4
Residual Offset Error (ppm of Range)	1,004.1
Offset Tempco (ppm of Range/°C)	7.8
INL Error (ppm of range)	61
Absolute Accuracy at Full Scale (μV)	40,941

Calculating Absolute Accuracy

$$AbsoluteAccuracy = OutputValue \times (GainError) + Range \times (OffsetError)$$

$$GainError = ResidualGainError + GainTempco \times (TempChangeFromLastInternalCal) + ReferenceTempco \times (TempChangeFromLastExternalCal)$$

$$OffsetError = ResidualOffsetError + AOffsetTempco \times (TempChangeFromLastInternalCal) + INL_Error$$

Refer to the following equation for an example of calculating absolute accuracy.

Absolute accuracy at full scale on the analog output channels is determined using the following assumptions:

- TempChangeFromLastExternalCal = 10 °C
- TempChangeFromLastInternalCal = 1 °C

$$\text{GainError} = 87.3 \text{ ppm} + 12.6 \text{ ppm} \times 1 + 4 \text{ ppm} \times 10$$

$$\text{GainError} = 139.9 \text{ ppm}$$

$$\text{OffsetError} = 41.1 \text{ ppm} + 7.8 \text{ ppm} \times 1 + 61 \text{ ppm}$$

$$\text{OffsetError} = 109.9 \text{ ppm}$$

$$\text{AbsoluteAccuracy} = 10 \text{ V} \times (\text{GainError}) + 10 \text{ V} \times (\text{OffsetError})$$

$$\text{AbsoluteAccuracy} = 2,498 \text{ } \mu\text{V}$$

DC Transfer Characteristics

INL	Refer to the AO Accuracy Table
DNL	± 0.5 LSB typical, ± 1 LSB maximum
Monotonicity	16 bits, guaranteed

Dynamic Characteristics

Table 8. Settling Time

Step Size (V)	Accuracy		
	± 16 LSB	± 4 LSB	± 2 LSB
± 20.0	5.3 μs	6.5 μs	7.8 μs
± 2.0	3.2 μs	3.9 μs	4.4 μs
± 0.2	1.8 μs	2.8 μs	3.8 μs

Slew rate	10 V/ μs
Noise	250 μVrms , DC to 1 MHz
Glitch energy at midscale transition	± 10 mV for 3 μs

5V Output

Output voltage	4.75 V to 5.1 V
Output current	0.5 A maximum

Overvoltage protection	± 30 V
Overcurrent protection	650 mA

Digital I/O

Table 9. Channel Frequency

Connector	Number of Channels	Maximum Frequency
Connector 0	16	10 MHz
Connector 1	32	80 MHz

Compatibility	LVTTL, LVCMOS
Logic family	Software-selectable
Default software setting	3.3 V

Table 10. Digital Input Logic Levels

Logic Family	Input Low Voltage (V_{IL}) Maximum	Input High Voltage (V_{IH}) Minimum
1.2 V	0.42 V	0.84 V
1.5 V	0.51 V	1.01 V
1.8 V	0.61 V	1.21 V
2.5 V	0.70 V	1.60 V
3.3 V	0.80 V	2.00 V

Minimum input	-0.3 V
Maximum input	3.6 V
Input leakage current	± 15 μ A maximum
Input impedance	50 k Ω typical, pull-down

Table 11. Digital Output Logic Levels

Logic Family	Current	Output Low Voltage (V_{OL}) Maximum	Output High Voltage (V_{OH}) Minimum
1.2 V	100 μ A	0.20 V	1.00 V
1.5 V	100 μ A	0.20 V	1.25 V

Table 11. Digital Output Logic Levels (Continued)

Logic Family	Current	Output Low Voltage (V _{OL}) Maximum	Output High Voltage (V _{OH}) Minimum
1.8 V	100 μ A	0.20 V	1.54 V
2.5 V	100 μ A	0.20 V	2.22 V
3.3 V	100 μ A	0.20 V	3.00 V
	4 mA	0.40 V	2.40 V

Maximum DC output current per channel

Source	4.0 mA
Sink	4.0 mA
Output impedance	50 Ω
Power-on state	Programmable, by line
Protection	\pm 20 V, single line ³
Digital I/O voltage selection	Programmable, per connector, and defined at compilation (not run-time configurable)
Direction control of digital I/O channels	Per channel
Minimum I/O pulse width	6.25 ns
Minimum sampling period	5 ns

External Clock

Direction	Input into device
Maximum input leakage	\pm 15 μ A
Characteristic impedance	50 Ω
Power-on state	Tristated
Minimum input	-0.3 V
Maximum input	3.6 V

³ NI recommends minimizing long-term over/under-voltage exposure to the Digital I/O. Prolonged DC voltage stresses that violate the maximum and minimum digital input voltage ratings may reduce device longevity. Over/under-voltage stresses are considered prolonged if the cumulative time in the abnormal condition exceeds 1 year.

Logic level	Inherited from programmed digital voltage selection per connector
Maximum input frequency	80 MHz

Reconfigurable FPGA

FPGA type	Kintex-7 160T
Number of flip-flops	202,800
Number of LUTs	101,400
Embedded Block RAM	11,700 kbits
Number of DSP48 slices	600
Timebase	40 MHz, 80 MHz, 120 MHz, 160 MHz, or 200 MHz
Default timebase	40 MHz
Timebase reference source	PXI Express 100 MHz (PXIe_CLK100)
Timebase accuracy	±100 ppm, 250 ps peak-to-peak jitter
Data transfers	DMA, interrupts, programmed I/O

Onboard DRAM

Memory size	1 Bank; 512 MB
Maximum theoretical data rate	800 MB/s streaming

Synchronization Resources

Input/output source	PXI_Trig<0..7>
Input source	PXI_Star, PXIe_DStarA, PXIe_DStarB, PXI_Clk10, PXIe_Clk100, External Clock 1
Output source	PXIe_DStarC

Bus Interface

Form factor	x4 PXI Express, specification v1.0 compliant
Slot compatibility	x4, x8, and x16 PXI Express or PXI Express hybrid slots

Data transfers	DMA, interrupts, programmed I/O
Number of DMA channels	16

Maximum Power Requirements

Power requirements are dependent on the digital output loads and configuration of the LabVIEW FPGA VI used in your application.

+3.3 V	3 A
+12 V	2 A

Physical Characteristics



Note If you need to clean the device, wipe it with a dry, clean towel.

Dimensions	18.5 cm × 17.3 cm × 3.6 cm (7.3 in. × 6.8 in. × 1.4 in.)
Weight	171.2 g (6.04 oz)
I/O connectors	2 × 68-pin VHDCI

Maximum Working Voltage

Maximum working voltage refers to the signal voltage plus the common-mode voltage.

Channel-to-earth	±12 V, Measurement Category I
Channel-to-channel	±24 V, Measurement Category I

Measurement Category I is for measurements performed on circuits not directly connected to the electrical distribution system referred to as MAINS voltage. MAINS is a hazardous live electrical supply system that powers equipment. This category is for measurements of voltages from specially protected secondary circuits. Such voltage measurements include signal levels, special equipment, limited-energy parts of equipment, circuits powered by regulated low-voltage sources, and electronics.



Caution Do not use the NI PXIe-7847R for connection to signals in Measurement Categories II, III, or IV.



Note Measurement Categories CAT I and CAT O (Other) are equivalent. These test and measurement circuits are not intended for direct connection to the MAINS building installations of Measurement Categories CAT II, CAT III, or CAT IV.

Safety

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



Note For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- EN 55022 (CISPR 22): Class A emissions
- EN 55024 (CISPR 24): Immunity
- AS/NZS CISPR 11: Group 1, Class A emissions
- AS/NZS CISPR 22: Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia and New Zealand (per CISPR 11) Class A equipment is intended for use only in heavy-industrial locations.



Note Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note For EMC declarations and certifications, and additional information, refer to the [Online Product Certification](#) section.

CE Compliance

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)

Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Shock and Vibration

Operational shock	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC 60068-2-27. Meets MIL-PRF-28800F Class 2 limits.)
Random vibration	
Operating	5 Hz to 500 Hz, 0.3 g _{rms}
Non-operating	.5 Hz to 500 Hz, 2.4 g _{rms} (Tested in accordance with IEC 60068-2-64. Meets MIL-PRF-28800F Class 3.)

Environmental

Refer to the manual for the chassis you are using for more information about meeting these specifications.

Operating temperature (IEC 60068-2-1, IEC 60068-2-2)	0 °C to 55 °C
Storage temperature (IEC 60068-2-1, IEC 60068-2-2)	-40 °C to 71 °C
Operating humidity (IEC 60068-2-56)	10% RH to 90% RH, noncondensing
Storage humidity (IEC 60068-2-56)	5% RH to 95% RH, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m

Indoor use only.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *Minimize Our Environmental Impact* web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

Waste Electrical and Electronic Equipment (WEEE)



EU Customers At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法（中国 RoHS）



中国客户 National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)

Calibration

Recommended warm-up time	15 minutes
Calibration interval	1 year
Onboard calibration reference	
DC level ⁴	5.000 V (±2 mV)
Temperature coefficient	±4 ppm/°C maximum
Long-term stability	±25 ppm/1,000 h



Note Refer to Calibration Certifications at ni.com/calibration to generate a calibration certificate for the NI PXIe-7847R.

Worldwide Support and Services

The NI website is your complete resource for technical support. At ni.com/support, you have access to everything from troubleshooting and application development self-help resources to email and phone assistance from NI Application Engineers.

Visit ni.com/services for NI Factory Installation Services, repairs, extended warranty, and other services.

Visit ni.com/register to register your NI product. Product registration facilitates technical support and ensures that you receive important information updates from NI.

⁴ Actual value stored in Flash memory

A Declaration of Conformity (DoC) is our claim of compliance with the Council of the European Communities using the manufacturer's declaration of conformity. This system affords the user protection for electromagnetic compatibility (EMC) and product safety. You can obtain the DoC for your product by visiting ni.com/certification. If your product supports calibration, you can obtain the calibration certificate for your product at ni.com/calibration.

NI corporate headquarters is located at 11500 North Mopac Expressway, Austin, Texas, 78759-3504. NI also has offices located around the world. For telephone support in the United States, create your service request at ni.com/support or dial 1 866 ASK MYNI (275 6964). For telephone support outside the United States, visit the *Worldwide Offices* section of ni.com/global to access the branch office websites, which provide up-to-date contact information, support phone numbers, email addresses, and current events.

Refer to the *NI Trademarks and Logo Guidelines* at ni.com/trademarks for information on NI trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering NI products/technology, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your media, or the *National Instruments Patent Notice* at ni.com/patents. You can find information about end-user license agreements (EULAs) and third-party legal notices in the readme file for your NI product. Refer to the *Export Compliance Information* at ni.com/legal/export-compliance for the NI global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data. NI MAKES NO EXPRESS OR IMPLIED WARRANTIES AS TO THE ACCURACY OF THE INFORMATION CONTAINED HEREIN AND SHALL NOT BE LIABLE FOR ANY ERRORS. U.S. Government Customers: The data contained in this manual was developed at private expense and is subject to the applicable limited rights and restricted data rights as set forth in FAR 52.227-14, DFAR 252.227-7014, and DFAR 252.227-7015.

© 2016 National Instruments. All rights reserved.

375945A-02 May16