

SPECIFICATIONS

PXIe-5785

PXI FlexRIO IF Transceiver

This document lists the specifications for the PXIe-5785. Specifications are subject to change without notice. For the most recent device specifications, refer to ni.com/support.



Note Using the PXIe-5785 in a manner not described in this document might impair the protection the PXIe-5785 provides.



Note These specifications are typical at 25 °C unless otherwise noted.



Note The PXIe-5785 requires a chassis with slot cooling capacity ≥ 58 W.

Contents

Definitions.....	2
Digital I/O.....	2
Digital I/O Single-Ended Channels.....	2
Digital I/O High-Speed Serial MGT.....	3
Reconfigurable FPGA.....	4
Onboard DRAM.....	5
Analog Input.....	5
General Characteristics.....	5
Typical Specifications.....	6
Analog Output.....	11
General Characteristics.....	11
Typical Specifications.....	11
REF/CLK IN.....	18
CLK/REF IN.....	18
Bus Interface.....	21
Maximum Power Requirements.....	21
Physical.....	22
Environment.....	22
Operating Environment.....	22
Storage Environment.....	22
Shock and Vibration.....	22
TCLK Specifications.....	23
Intermodule SMC Synchronization Using NI-TClk for Identical Modules.....	23

Definitions

Warranted specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

Characteristics describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- *Typical* specifications describe the performance met by a majority of models.
- *Nominal* specifications describe an attribute that is based on design, conformance testing, or supplemental testing.

Specifications are *Typical* unless otherwise noted.

Digital I/O

Connector	Molex™ Nano-Pitch I/O™
5.0 V Power	±5%, 50 mA maximum, nominal

Table 1. Digital I/O Signal Characteristics

Signal	Type	Direction
MGT Tx± <3..0> ¹	Xilinx UltraScale GTH	Output
MGT Rx± <3..0> ¹	Xilinx UltraScale GTH	Input
DIO <7..0>	Single-ended	Bidirectional
5.0 V	DC	Output
GND	Ground	—

Digital I/O Single-Ended Channels

Number of channels	8
Signal type	Single-ended
Voltage families	3.3 V, 2.5 V, 1.8 V, 1.5 V, 1.2 V
Input impedance	100 kΩ, nominal
Output impedance	50 Ω, nominal
Direction control	Per channel

¹ Multi-gigabit transceiver (MGT) signals are available on devices with KU040 and KU060 FPGAs only.

Minimum required direction change latency	200 ns
Maximum output toggle rate	60 MHz with 100 μ A load, nominal

Table 2. Digital I/O Single-Ended DC Signal Characteristics²

Voltage Family	V _{IL}	V _{IH}	V _{OL} (100 μ A load)	V _{OH} (100 μ A load)	Maximum DC Drive Strength
3.3 V	0.8 V	2.0 V	0.2 V	3.0 V	24 mA
2.5 V	0.7 V	1.6 V	0.2 V	2.2 V	18 mA
1.8 V	0.62 V	1.29 V	0.2 V	1.5 V	16 mA
1.5 V	0.51 V	1.07 V	0.2 V	1.2 V	12 mA
1.2 V	0.42 V	0.87 V	0.2 V	0.9 V	6 mA

Digital I/O High-Speed Serial MGT³



Note MGTs are available on devices with KU040 and KU060 FPGAs only.

Data rate	500 Mbps to 16.375 Gbps, nominal
Number of Tx channels	4
Number of Rx channels	4
I/O AC coupling capacitor	100 nF

² Voltage levels are guaranteed by design through the digital buffer specifications.

³ For detailed FPGA and High-Speed Serial Link specifications, refer to Xilinx documentation.

Figure 1. Digital I/O Connector

Reserved	A1	B1	5.0 V
GND	A2	B2	GND
MGT Rx+ 0	A3	B3	MGT Tx+ 0
MGT Rx- 0	A4	B4	MGT Tx- 0
GND	A5	B5	GND
MGT Rx+ 1	A6	B6	MGT Tx+ 1
MGT Rx- 1	A7	B7	MGT Tx- 1
GND	A8	B8	GND
DIO 4	A9	B9	DIO 6
DIO 5	A10	B10	DIO 7
GND	A11	B11	GND
MGT REF+ / DIO 0	A12	B12	DIO 2
MGT REF- / DIO 1	A13	B13	DIO 3
GND	A14	B14	GND
MGT Rx+ 2	A15	B15	MGT Tx+ 2
MGT Rx- 2	A16	B16	MGT Tx- 2
GND	A17	B17	GND
MGT Rx+ 3	A18	B18	MGT Tx+ 3
MGT Rx- 3	A19	B19	MGT Tx- 3
GND	A20	B20	GND
5.0 V	A21	B21	Reserved

Reconfigurable FPGA

PXIe-5785 modules are available with multiple FPGA options. The following table lists the FPGA specifications for the PXIe-5785 FPGA options.

Table 3. Reconfigurable FPGA Options

	KU035	KU040	KU060
LUTs	203,128	242,200	331,680
DSP48 slices (25 × 18 multiplier)	1,700	1,920	2,760
Embedded Block RAM	19.0 Mb	21.1 Mb	38.0 Mb
Data Clock Domain	200 MHz, 16 samples per cycle per channel (dual channel mode), 32 samples per cycle (single channel mode)		

Table 3. Reconfigurable FPGA Options (Continued)

	KU035	KU040	KU060
Timebase reference sources	PXI Express 100 MHz (PXIe_CLK100)		
Data transfers	DMA, interrupts, programmed I/O	DMA, interrupts, programmed I/O, multi-gigabit transceivers	
Number of DMA channels	60		



Note The Reconfigurable FPGA Options table depicts the total number of FPGA resources available on the part. The number of resources available to the user is slightly lower, as some FPGA resources are consumed by board-interfacing IP for PCI Express, device configuration, and various board I/O. For more information, contact NI support.

Onboard DRAM

Memory size	4 GB (2 banks of 2 GB)
DRAM clock rate	1064 MHz
Physical bus width	32 bit
LabVIEW FPGA DRAM clock rate	267 MHz
LabVIEW FPGA DRAM bus width	256 bit per bank
Maximum theoretical data rate	17 GB/s (8.5 GB/s per bank)

Analog Input

General Characteristics

Number of channels	2, single-ended, simultaneously sampled
Connector type	SMA
Input impedance	50 Ω
Input coupling	AC
Sample Clock	
Internal Sample Clock	3.2 GHz
External Sample Clock	2.0 GHz to 3.2 GHz

Sample Rate

Dual channel mode	3.2 GS/s per channel
Single channel mode	6.4 GS/s
Analog-to-digital converter (ADC)	ADC12DJ3200, 12-bit resolution

Typical Specifications

Full-scale input range	1.25 V pk-pk (5.92 dBm) at 10 MHz
AC gain accuracy	±0.11 dB at 10 MHz
DC offset	±2.19 mV
Bandwidth (-3 dB) ⁴	500 kHz to 6 GHz

Table 4. Single-Tone Spectral Performance, Dual Channel Mode

	Input Frequency				
	99.9 MHz	399 MHz	999 MHz	1.999 GHz	2.499 GHz
SNR ⁵ (dBFS)	56.0	55.6	54.7	52.9	51.6
SINAD ⁵ (dBFS)	55.5	55.0	54.0	51.8	50.8
SFDR (dBc)	-64.9	-63.4	-62.7	-59.9	-58.6
ENOB ⁶ (bits)	8.9	8.8	8.7	8.3	8.1

Table 5. Single-Tone Spectral Performance, Single Channel Mode⁷

	Input Frequency				
	99.9 MHz	399 MHz	999 MHz	1.999 GHz	2.499 GHz
SNR ⁵ (dBFS)	54.6	54.2	52.4	49.7	48.9
SINAD ⁵ (dBFS)	54.4	53.9	52.1	49.4	48.6
SFDR (dBc)	-61.7	-60.4	-56.1	-51.7	-51.1
ENOB ⁶ (bits)	8.7	8.7	8.4	7.9	7.8

⁴ Normalized to 10 MHz.

⁵ Measured with a -1 dBFS signal and corrected to full-scale. 3.2 kHz resolution bandwidth.

⁶ Calculated from SINAD and corrected to full scale.

⁷ Measured using channel A10. Spectral performance may be degraded using channel A11.


Table 6. Noise Spectral Density⁸

Mode	$\frac{nV}{\sqrt{Hz}}$	$\frac{dBm}{Hz}$	$\frac{dBFS}{Hz}$
Dual channel	14.4	-143.8	-149.2
Single channel	9.8	-147.2	-152.6



Note Noise spectral density is verified using a 50 Ω terminator connected to the input.

Figure 2. Single Tone Spectrum (Dual Channel Mode, 99.9 MHz, -1 dBFS, 3.2 kHz RBW), Measured



⁸ Excludes fixed interleaving spur (Fs/2 spur).

Figure 3. Single Tone Spectrum (Dual Channel Mode, 1.999 GHz, -1 dBFS, 3.2 kHz RBW), Measured




Figure 4. Single Tone Spectrum (Single Channel Mode, 99.9 MHz, -1 dBFS, 3.2 kHz RBW), Measured





Figure 5. Single Tone Spectrum (Single Channel Mode, 1.999 GHz, -1 dBFS, 3.2 kHz RBW), Measured



Channel-to-channel crosstalk

99.9 MHz	-92.5 dB
399 MHz	-85.5 dB
999 MHz	-76.5 dB
1.999 GHz	-68.8 dB
2.499 GHz	-67.4 dB

Figure 6. Analog Input Frequency Response, Measured





Figure 7. Input Return Loss, Measured



Analog Output

General Characteristics

Number of channels	2, single-ended, simultaneously updated
Connector type	SMA
Output impedance	50 Ω
Output coupling	AC
Update rate	
Internal Sample Clock, 2x interpolation	6.4 GS/s
External Sample Clock, 2x interpolation	6.4 GS/s ⁹
Data rate (per channel)	
Dual channel mode	3.2 GS/s, real
Single channel mode	3.2 GS/s, complex
Digital-to-analog converter (DAC)	DAC38RF82, 12-bit resolution

Typical Specifications

Full-scale output power ¹⁰	
Dual Channel Mode	2.85 dBm (878 mVpp)
Single Channel Mode	-3.33 dBm (431 mVpp)
Bandwidth (-3 dB) ¹¹	
Dual Channel Mode	3 MHz to 1.53 GHz
Single Channel Mode (no anti-image filter)	60 MHz to 2.85 GHz
Single Channel Mode (with anti-image filter)	60 MHz to 2.35 GHz

⁹ To achieve this update rate when using an external sample clock, inject a 3.2 GS/s clock into the REF/CLK IN port and enable 2x interpolation.

¹⁰ Into a 50 Ω load.

¹¹ Normalized to 10 MHz in dual channel mode and 200 MHz in single channel mode. 2x interpolation and inverse sinc filter enabled.

Table 7. Single Tone Spectral Performance, Dual Channel Mode¹²

	Generation Frequency	
	501 MHz	1.01 GHz
2nd HD (dBc)	-67.8	-61.7
3rd HD (dBc)	-63.0	-62.0
SFDR (dBc)	-63.0	-61.7

Table 8. Single Tone Spectral Performance, Single Channel Mode¹²

	Generation Frequency
	1.01 GHz
2nd HD (dBc)	-62.4
3rd HD (dBc)	-67.3
SFDR (dBc)	-62.4

Table 9. IMD3 Performance, Dual Channel Mode¹³

	Generation Frequency	
	501 MHz and 511 MHz	1.005 GHz and 1.015 GHz
IMD3 (dBc)	-73.9	-67.6

Table 10. Noise Spectral Density¹⁴

Mode	501 MHz Generation Frequency		
	$\frac{nV}{\sqrt{Hz}}$	$\frac{dBm}{Hz}$	$\frac{dBFS}{Hz}$
Dual Channel	1.18	-165.5	-168.4
Single Channel	0.941	-167.5	-164.2

¹² DC, 3.2 GHz, output corrected to 0 dBFS by inverse sinc filter, 2x interpolation, no anti-image filter.

¹³ 2x interpolation, inverse sinc filter enabled, each tone corrected to -6 dBFS by inverse sinc filter.

¹⁴ Measured > 50 MHz offset from fundamental. 2x interpolation and inverse sinc filter enabled. Noise spectral density value depends on output tone frequency. See DAC38RF82 datasheet for noise spectral density results at other tone frequencies.

Figure 8. Single Tone Spectrum (Dual Channel Mode, 501 MHz 0 dBFS), Measured¹⁵






Figure 9. Single Tone Spectrum (Dual Channel Mode, 1.01 GHz 0 dBFS), Measured¹⁵



¹⁵ 2x interpolation. Output corrected to 0 dBFS by inverse sinc filter. 10 kHz resolution bandwidth.


Figure 10. Single Tone Spectrum (Single Channel Mode, 1.01 GHz 0 dBFS),
Measured¹⁵



Channel-to-channel crosstalk, measured

100 MHz	-82 dBc
500 MHz	-91 dBc
1.0 GHz	-90 dBc
1.5 GHz	-88 dBc
2.0 GHz	-82 dBc
2.5 GHz	-82 dBc

Figure 11. Analog Output Dual Channel Mode Frequency Response, Measured ¹⁶



¹⁶ -6 dBFS, 2x Interpolation, inverse sinc filter enabled, no anti-image filter, normalized to 200 MHz.

Figure 12. Analog Output Single Channel Mode Frequency Response, No Anti-Image Filter, Measured¹⁶






Figure 13. Analog Output Single Channel Mode Frequency Response With Anti-Image Filter, Measured¹⁷



¹⁷ -6 dBFS, 2x Interpolation, inverse sinc filter enabled, normalized to 200 MHz.

Figure 14. Analog Output Return Loss, Measured



REF/CLK IN

CLK/REF IN

Connector type	SMA
Input impedance	50 Ω
Input coupling	AC
Input voltage range	0.35 V pk-pk to 3.5 V pk-pk, nominal
Absolute maximum voltage	± 12 V DC, 4 V pk-pk AC
Duty cycle	45% to 55%

Sample Clock jitter

Analog input	86.8 fs _{rms} , measured ¹⁸
Analog output	198.8 fs _{rms} , measured ¹⁹

Table 11. Clock Configuration Options

Clock Configuration	External Clock Frequency	Description
Internal PXI_CLK10 ²⁰	10 MHz	The internal Sample Clock locks to the PXI 10 MHz Reference Clock, which is provided through the backplane.
External Reference Clock (CLK/REF IN)	10 MHz ²¹	The internal Sample Clock locks to an external Reference Clock, which is provided through the CLK/REF IN front panel connector.
External Sample Clock (CLK/REF IN)	2.8 GHz to 3.2 GHz	An external Sample Clock can be provided through the CLK/REF IN front panel connector.

¹⁸ Integrated from 3.2 kHz to 20 MHz. Includes the effects of the converter aperture uncertainty and the clock circuitry jitter. Excludes trigger jitter.

¹⁹ Integrated from 1 kHz to 30 MHz. Includes the effects of the converter aperture uncertainty, converter PLL circuitry, and the clock circuitry jitter. Excludes trigger jitter.

²⁰ Default clock configuration.

²¹ The external Reference Clock must be accurate to ± 25 ppm.

Figure 15. Analog Input Phase Noise with 800 MHz Input Tone, Measured





Figure 16. Analog Output Phase Noise with 1 GHz Output Tone, Measured



Bus Interface

Form factor	x8 PXI Express, specification v2.1 compliant
Slot compatibility	x4, x8, and x16 PXI Express or PXI Express hybrid slots

Maximum Power Requirements



Note Power requirements are dependent on the contents of the LabVIEW FPGA VI used in your application.

+3.3 V	3 A
+12 V	4 A
Maximum total power	58 W

Physical

Dimensions (not including connectors)	18.8 cm × 12.9 cm (7.4 in. × 5.1 in.)
Weight	190 g (6.7 oz)

Environment

Maximum altitude	2,000 m (800 mbar) (at 25 °C ambient temperature)
Pollution Degree	2

Indoor use only.

Operating Environment

Ambient temperature range	0 °C to 55 °C ²² (Tested in accordance with IEC 60068-2-1 and IEC 60068-2-2. Meets MIL-PRF-28800F Class 3 low temperature limit and MIL-PRF-28800F Class 2 high temperature limit.)
Relative humidity range	10% to 90%, noncondensing (Tested in accordance with IEC 60068-2-56.)

Storage Environment

Ambient temperature range	-40 °C to 71 °C (Tested in accordance with IEC 60068-2-1 and IEC 60068-2-2. Meets MIL-PRF-28800F Class 4 limits.)
Relative humidity range	5% to 95%, noncondensing (Tested in accordance with IEC 60068-2-56.)

Shock and Vibration

Operating shock	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC 60068-2-27. Meets MIL-PRF-28800F Class 2 limits.)
-----------------	--

²² The PXIe-5785 requires a chassis with slot cooling capacity ≥ 58 W. Not all chassis with slot cooling capacity ≥ 58 W can achieve this ambient temperature range. Refer to the [PXI Chassis Manual](#) for specifications to determine the ambient temperature ranges your chassis can achieve.

Random vibration

Operating	5 Hz to 500 Hz, 0.3 g_{rms} (Tested in accordance with IEC 60068-2-64.)
Nonoperating	5 Hz to 500 Hz, 2.4 g_{rms} (Tested in accordance with IEC 60068-2-64. Test profile exceeds the requirements of MIL-PRF-28800F, Class 3.)

TCLK Specifications

You can use the NI TCLK synchronization method and the NI-TCLK driver to align the Sample Clocks on any number of supported devices, in one or more chassis. For more information about TCLK synchronization, refer to the *NI-TCLK Synchronization Help* within the *FlexRIO Help*. For other configurations, including multichassis systems, contact NI Technical Support at ni.com/support.

Intermodule SMC Synchronization Using NI-TCLK for Identical Modules

Synchronization specifications are valid under the following conditions:

- All modules are installed in one PXI Express chassis.
- The NI-TCLK driver is used to align the Sample Clocks of each module.
- All parameters are set to identical values for each module.
- Modules are synchronized without using an external Sample Clock.



Note Although you can use NI-TCLK to synchronize non-identical SMC-based modules, these specifications apply only to synchronizing identical modules.

Skew ²³	80 ps, measured
Skew after manual adjustment	≤10 ps, measured
Sample Clock delay/adjustment	0.4 ps

²³ Caused by clock and analog delay differences. No manual adjustment performed. Tested with a PXIe-1085 chassis with a 24 GB backplane with a maximum slot to slot skew of 100 ps. Measured at 23 °C.

Information is subject to change without notice. Refer to the *NI Trademarks and Logo Guidelines* at ni.com/trademarks for information on NI trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering NI products/technology, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your media, or the *National Instruments Patent Notice* at ni.com/patents. You can find information about end-user license agreements (EULAs) and third-party legal notices in the `readme` file for your NI product. Refer to the *Export Compliance Information* at ni.com/legal/export-compliance for the NI global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data. NI MAKES NO EXPRESS OR IMPLIED WARRANTIES AS TO THE ACCURACY OF THE INFORMATION CONTAINED HEREIN AND SHALL NOT BE LIABLE FOR ANY ERRORS. U.S. Government Customers: The data contained in this manual was developed at private expense and is subject to the applicable limited rights and restricted data rights as set forth in FAR 52.227-14, DFAR 252.227-7014, and DFAR 252.227-7015.

© 2017 National Instruments. All rights reserved.

376898A-01 October 8, 2018