

Compact FieldPoint LabVIEW Real-Time Controllers with Ethernet

NI cFP-21xx **NEW!**

- Rugged LabVIEW Real-Time controller
 - 188 MHz processor and up to 128 MB of SDRAM
 - Up to 128 MB of nonvolatile storage and 512 MB removable CompactFlash
- Ethernet communication for distributed real-time systems
- Dual redundant 11 to 30 VDC power supply inputs, low power
- Up to 4 serial ports (3 RS232 and 1 RS485) for communication
- Industrial certifications, Class I, Div 2, and -40 to 70 °C

Operating Systems

- Windows XP/2000/NT
- LabVIEW Real-Time

Recommended Software

- LabVIEW
- LabVIEW Real-Time Module
- LabVIEW Datalogging and Supervisory Control Module

Driver Software (included)

- Measurement & Automation Explorer
- OPC server (2.0 compliant)



Controller	SDRAM Memory (MB)	Internal Nonvolatile Storage (MB)	Removable CompactFlash	Ethernet Ports	RS232 Ports	RS485 Ports
cFP-2120	128	128	✓	1	3	1
cFP-2110	128	64	–	1	2	0
cFP-2100	64	64	–	1	1	0

Table 1. cFP-21xx Selection Guide

Overview

National Instruments Compact FieldPoint is a programmable automation controller (PAC) designed for industrial control applications performing advanced embedded control, data logging, and network connectivity. It combines the packaging, specifications, and reliability of a PLC with the software, flexibility, connectivity, and functionality of a PC. Compact FieldPoint is a reliable platform designed for rugged industrial environments with shock, vibration, and temperature extremes.

National Instruments cFP-21xx controllers run LabVIEW Real-Time, providing the functionality, connectivity, and flexibility of NI LabVIEW software on a small industrial platform. The modular I/O architecture with built-in signal conditioning and isolation provides direct connectivity to industrial sensors such as analog voltage, 4 to 20 mA current, thermocouples, RTDs, pressure, strain, flow, pulse-width modulation (PWM), and 24 V digital I/O. You can use NI cFP-21xx controllers in intelligent distributed applications requiring industrial-grade reliability – such as process and discrete control systems – to open and close valves, run control loops, log data on a centralized or local level, perform real-time simulation and analysis, and communicate over serial and Ethernet networks.

System Basics

A single cFP-21xx controller manages a bank of up to eight Compact FieldPoint I/O modules. The controller mounts securely on a metal backplane that provides the communication bus as well as a solid surface for the Compact FieldPoint I/O modules and controller. The system is modular; select the I/O modules and connector blocks or cabling options best suited for your application. Compact FieldPoint I/O banks have a number of features for industrial operation, including 2,300 V transient overvoltage protection, a wide temperature range for operation in extreme environments, backup power supply connections to protect against primary power failure, and hot-swappable modules to simplify maintenance and minimize downtime. cFP-21xx controllers feature an industrial 188 MHz x86 processor that reliably and deterministically executes your LabVIEW Real-Time applications.

Choose from thousands of built-in LabVIEW functions to build your multithreaded embedded system for real-time control, analysis, data logging, and communication. cFP-21xx controllers also offer up to 128 MB of 100 MHz SDRAM and 128 MB of internal nonvolatile storage and a removable CompactFlash slot. All cFP-21xx controllers feature a 10/100 Mb/s Ethernet port for communication over the network (including e-mail) and built-in Web (HTTP) and file servers (FTP). Using the LabVIEW Remote Panel feature, you can automatically publish the front panel graphical user interface (GUI) for your embedded application so that multiple clients can monitor or control it remotely using a Web browser.

Compact FieldPoint LabVIEW Real-Time Controllers with Ethernet




Figure 3. Expansion I/O for cFP-21xx Controllers with NI cFP-1808 Network Interface

Embedded Data Logging

The cFP-2120 features 128 MB of nonvolatile removable CompactFlash storage for data logging or additional storage capacity. You can store the data in standard format, including CSV and XML. Once you store the data, you can easily transfer it to a PC using the embedded FTP server on the cFP-21xx. LabVIEW Real-Time expands the functionality beyond the typical data logger because you can make additional calculations and decisions to eliminate logging unneeded data and to perform onboard real-time calculations. Compact FieldPoint combines data logging, data reduction, control algorithms, a Web-based human machine interface (HMI), and the ability to communicate with other nodes on the network.

Communication

A cFP-21xx controller connects directly to your network through the built-in Ethernet port. The Ethernet port serves as a high-speed link for downloading application code, performing run-time debugging and probing, and transmitting control and indicator values with a GUI running on a networked PC. You also can use the Ethernet port for programmatic network communication using standard protocols such as TCP, UDP, FTP, HTTP, and DataSocket. Once deployed, the controller can communicate with any Ethernet-enabled device on the network. In addition, a cFP-21xx can communicate with a Windows computer running LabVIEW or any third-party HMI/SCADA software compatible with OPC. By using LabVIEW libraries and industrial gateways, you can add a Compact FieldPoint bank to any existing setup and communicate with industrial devices through standard communication protocols such as Modbus TCP and PROFIBUS.

Serial Connectivity

cFP-21xx controllers have up to three RS232 serial ports and one RS485 port (cFP-2120) to communicate programmatically with other serial devices such as remote FieldPoint banks, LCD display/keypad units, bar code readers, or phone and radio modems.

Power Supply Backup and Regulation

cFP-21xx controllers require an 11 to 30 VDC power supply. An extra set of screw terminals is available on the network controllers for a backup UPS or battery. The controller filters and regulates the power input, redistributing power to all the I/O modules in the node through the backplane bus. Refer to Ordering Information for suitable power supplies.

Ordering Information

NI cFP-2120	777317-2120
NI cFP-2110	777317-2110
NI cFP-2100	777317-2100

Recommended Compact FieldPoint System Products

NI cFP-BP-4 (4-slot backplane).....	778617-04
NI cFP-BP-8 (8-slot backplane).....	778617-08
NI cFP-CB-1 (internal connector block)	778618-01
NI cFP-CB-3 (isothermal connector block)	778618-03
NI PS-5 Power Supply	778805-90

BUY NOW!

For complete product specifications, pricing, and accessory information, call 800 813 3693 (U.S.) or go to ni.com/fieldpoint.

Compact FieldPoint LabVIEW Real-Time Controllers with Ethernet

Specifications

Network

Network interface.....	10BaseT and 100BaseTX Ethernet
Compatibility.....	IEEE802.3
Communication rates.....	10 Mb/s, 100 Mb/s, autonegotiated
Maximum cabling distance.....	100 m/segment
Maximum number of banks.....	Determined by network topology

Memory

cFP-2100.....	64 MB nonvolatile; 64 MB DRAM
cFP-2110.....	64 MB nonvolatile; 128 MB DRAM
cFP-2120.....	128 MB nonvolatile; 128 MB DRAM
Memory lifetime (nonvolatile).....	300,000 writes per sector

For information about the memory used by the LabVIEW Real-Time Module and the OS, go to ni.com/info and enter **rdlpec**.

Serial Ports

cFP-2100.....	1 RS232
cFP-2110.....	2 RS232
cFP-2120.....	3 RS232; 1 RS485

RS232 (DTE) Ports

Baud rate.....	110 to 115,200 b/s
Data bits.....	5, 6, 7, 8
Stop bits.....	1, 1.5, 2
Parity.....	Odd, even, mark, space
Flow control.....	RTS/CTS, XON/XOFF, DTR/DSR

RS485 (DTE) Port

Baud rate.....	110 to 115,200 b/s
Data bits.....	5, 6, 7, 8
Stop bits.....	1, 1.5, 2
Parity.....	Odd, even, mark, space
Flow control.....	XON/XOFF
Mode.....	4-wire
Maximum continuous	
Isolation voltage.....	100 V _{rms}
Dielectric withstand.....	740 V _{rms} , 1 minute

Power Requirement

Power supply range.....	11 to 30 VDC
Recommended power supply	
cFP-BP-4 system.....	15 W
cFP-BP-8 system.....	20 W
Power consumption.....	6.1 W + 1.1(I/O module power requirements)
Maximum power to connected I/O modules.....	9 W

Physical Characteristics

Screw-terminal wiring.....	16 to 26 AWG copper conductor wire with 7 mm (0.28 in.) of insulation stripped from the end
Torque for screw terminals.....	0.5 to 0.6 N•m (4.4 to 5.3 lb•in.)
Weight.....	278 g (9.8 oz)

Compact FieldPoint LabVIEW Real-Time Controllers with Ethernet

Environmental

FieldPoint modules are intended for indoor use only. For outdoor use, they must be installed in a suitable sealed enclosure.

Operating temperature	-40 to 70 °C
Storage temperature.....	-55 to 85 °C
Relative humidity	10 to 90%, noncondensing
Maximum altitude.....	2,000 m; at higher altitudes the isolation voltage ratings must be lowered
Pollution degree.....	2

Shock and Vibration

Operating vibration	
Random (IEC 60068-2-64).....	10 to 500 Hz, 5 g _{rms}
Sinusoidal (IEC 60068-2-6)	10 to 500 Hz, 5 g
Operating shock	
(IEC 60068-2-27)	50 g, 3 ms half sine, 18 shocks at 6 orientations; 30 g, 11 ms half sine, 18 shocks at 6 orientations

Safety

This product is designed to meet the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1

Note: For UL and other safety certifications, refer to the product label or visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Electromagnetic Compatibility

This product is designed to meet the requirements of the following standards of EMC for electrical equipment for measurement, control, and laboratory use:

- EN 61326 EMC requirements; Industrial Immunity
- EN 55011 Emissions; Group 1, Class A
- CE, C-Tick, ICES, and FCC Part 15 Emissions; Class A

Note: For EMC compliance, operate this device according to product documentation.

CE Compliance

This product meets the essential requirements of applicable European Directives, as amended for CE marking, as follows: Low-Voltage Directive (safety)

- 73/23/EEC; Low-Voltage Directive (safety)
- 89/336/EEC; Electromagnetic Compatibility Directive (EMC)

Note: Refer to the Declaration of Conformity (DoC) for this product for any additional regulatory compliance information. To obtain the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Waste Electrical and Electronic Equipment (WEEE)

EU Customers: At the end of their life cycle, all products must be sent to a WEEE recycling center. For more information about WEEE recycling centers and National Instruments WEEE initiatives, visit ni.com/environment/weee.htm.

NI Services and Support



NI has the services and support to meet your needs around the globe and through the application life cycle – from planning and development through deployment and ongoing maintenance. We offer services and service levels to meet customer requirements in research, design, validation, and manufacturing. Visit ni.com/services.

Training and Certification

NI training is the fastest, most certain route to productivity with our products. NI training can shorten your learning curve, save development time, and reduce maintenance costs over the application life cycle. We schedule instructor-led courses in cities worldwide, or we can hold a course at your facility. We also offer a professional certification program that identifies individuals who have high levels of skill and knowledge on using NI products. Visit ni.com/training.

Professional Services

Our NI Professional Services team is composed of NI applications and systems engineers and a worldwide National Instruments Alliance Partner program of more than 600 independent consultants and

integrators. Services range from start-up assistance to turnkey system integration. Visit ni.com/alliance.



OEM Support

We offer design-in consulting and product integration assistance if you want to use our products for OEM applications. For information about special pricing and services for OEM customers, visit ni.com/oem.

Local Sales and Technical Support

In offices worldwide, our staff is local to the country, giving you access to engineers who speak your language. NI delivers industry-leading technical support through online knowledge bases, our applications engineers, and access to 14,000 measurement and automation professionals within NI Developer Exchange forums. Find immediate answers to your questions at ni.com/support.

We also offer service programs that provide automatic upgrades to your application development environment and higher levels of technical support. Visit ni.com/ssp.

Hardware Services

NI Factory Installation Services

NI Factory Installation Services (FIS) is the fastest and easiest way to use your PXI or PXI/SCXI combination systems right out of the box. Trained NI technicians install the software and hardware and configure the system to your specifications. NI extends the standard warranty by one year on hardware components (controllers, chassis, modules) purchased with FIS. To use FIS, simply configure your system online with ni.com/pxiadvisor.

Calibration Services

NI recognizes the need to maintain properly calibrated devices for high-accuracy measurements. We provide manual calibration procedures, services to recalibrate your products, and automated calibration software specifically designed for use by metrology laboratories. Visit ni.com/calibration.

Repair and Extended Warranty

NI provides complete repair services for our products. Express repair and advance replacement services are also available. We offer extended warranties to help you meet project life-cycle requirements. Visit ni.com/services.



ni.com • 800 813 3693

National Instruments • info@ni.com

