

Rack Mounting of Signal Conditioning Accessories

Rack Mounting Kits

For


- SC-204x Series
- SC-205x Series
- SC-206x Series
- SC-207x Series
- BNC-208x Series
- AMUX-64T

Single or double-height kits
Acrylic plastic or metal wraparound cover

Single-Height Rack-Mount Kit with Acrylic Plastic Cover

Rack-Mount Kits

Double-Height Rack-Mount Kit with Metal Wraparound Cover



Description

Rack-mount kits hold signal conditioning accessories, such as the AMUX-64T analog multiplexer and SC Series signal conditioning boards, in standard 19 in. rack-mount cabinets. The rack-mount kits are available with either an acrylic plastic or metal wraparound cover. The kits with metal wraparound covers are safe for high-voltage applications. Both the acrylic plastic cover and the metal wrap around cover kits are available in either single or double-height kits and therefore reduce the cost of large systems. The metal wraparound cover is not recommended for use with the BNC-208x Series.

Rack-mount accessories are also available for our SCXI chassis. See page 404 for more informations on SCXI rack mounts or panel mounts.

Mounting

The rack-mount kits accommodate many of our accessories. The table at left shows how much space each accessory requires in a single-height rack-mount kit. For example, three SC-2050 boards or will fit into one rack-mount kit. You can intermix SC accessories in a rack-mount kit.

Accessory	Width Required
AMUX-64T	Two-thirds
SC-2040, SC-2042-RTD, SC-2043-SG	One-half
SC-2050, SC-2051, SC-2052 SC-2053, SC-2055, SC-2057	One-third
SC-2054, SC-2056	One-half
SC-206x Series	One-third
SC-207x Series	One-half
BNC-208x Series	One-half

Ordering Information

Rack-mount kit with acrylic plastic cover

Single-height777212-01

Double-height.....777212-02

Rack-mount kit with metal wraparound cover

Single-height777212-11

Double-height777212-12