

Extender Cables and Rack-Mount Kits

T7 Cable*

Fiber-optic cable assembly for GPIB-140A

Connector – ST; operating wavelength – 850 nm; core/clad – 62.5/125 μ m

50 m.....	182805-050
100 m.....	182805-100
500 m.....	182805-500



T7 Cable (GPIB-140A)

T8 Cable*

Fiber-optic cable assembly for GPIB-140A/2

Connector – ST; operating wavelength – 1,300 nm; core/clad – 62.5/125 μ m

1,000 m.....	183164-01K
2,000 m.....	183164-02K

*For other cable lengths, contact National Instruments.

CS2 Rack-Mount Kit for GPIB-120A

Single case.....	776849-01
Dual case.....	776849-02



CS2 Rack-Mount Kit for GPIB-120A (Dual Case)

Rack-Mount Kit for GPIB-ENET/100, ENET-232 or ENET-485

Single/dual case.....	187322-02
-----------------------	-----------



Rack-Mount Kit for GPIB-ENET/100

DIN-Rail/Wall-Mount Kit for GPIB-ENET/100, ENET-232, or ENET-485

Single unit.....	777972-01
------------------	-----------



DIN-Rail/Wall-Mount Kit for GPIB-ENET/100