

# 2.0 GHz Dual-Core Embedded Controller for PXI Express

## NI PXIe-8105

- Intel Core Duo processor T2500 (2.0 GHz dual core)
- Up to 1 GB/s system bandwidth
- Up to 1 GB/s slot bandwidth
- 512 MB (1 x 512 MB DIMM) dual-channel 667 MHz DDR2 RAM standard, 4 GB (2 x 2 GB DIMMs) maximum
- Integrated I/O
  - 10/100/1000BASE-TX Ethernet
  - 4 Hi-Speed USB ports
  - ExpressCard/34 slot
  - DVI-I video connector
  - GPIB (IEEE 488) controller
  - RS232 serial port
  - IEEE 1284 ECP/EPP parallel port
  - Integrated hard drive
- Internal PXI trigger bus routing
- Watchdog timer

### Software

- OS and drivers already installed
- Hard drive-based recovery image

### PXI Express System Configuration

- Complete PXI Express system configuration at [ni.com/pxiadvisor](http://ni.com/pxiadvisor)



## Overview

The National Instruments PXIe-8105 is a high-performance Intel Core Duo processor T2500-based embedded controller for use in PXI Express and CompactPCI Express systems. With its 2.0 GHz dual-core processor and dual-channel 667 MHz DDR2 memory, the NI PXIe-8105 is ideal for applications requiring intensive analysis or system development. An NI PXIe-8105 embedded controller in a PXI Express chassis, such as the NI PXIe-1062Q, offers a compact, high-performance PC platform for modular instrumentation and data acquisition applications.

CPU	Intel Core Duo processor T2500 (2.0 GHz Dual Core)
Front-side bus	667 MHz
L2 cache	2048 KB
System bandwidth	Up to 1 GB/s
Slot bandwidth	Up to 1 GB/s
PXI Express 4-link configuration	3 x4 links and 1 x1 link
PXI Express 2-link configuration	2 x4 links
Dual-channel 667 MHz DDR2 RAM, standard	512 MB (1 x 512 MB)
Dual-channel 667 MHz DDR2 RAM, maximum	4 GB (2 x 2 GB)
Hard drive, minimum	60 GB SATA <sup>1</sup>
10/100/1000BASE-TX Ethernet	✓
GPIB (IEEE 488) controller	✓
Serial port (RS232)	✓
Parallel port	✓
Hi-Speed USB ports	4
ExpressCard/34 slot	✓
PS/2 keyboard/mouse connector	- 2
Watchdog/trigger SMB	✓
Installed OS	Windows XP Professional <sup>3</sup>

<sup>1</sup>30 GB PATA hard drive for extended temperature option

<sup>2</sup>For a legacy PS/2 keyboard and mouse, add the USB-to-dual-PS/2 adapter

<sup>3</sup>Contact National Instruments or visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor) for information on other available operating systems

Table 1. NI PXIe-8105 Features

## Dual-Core Processor

The NI PXIe-8105 includes the dual-core Intel Core Duo processor T2500. Dual-core processors contain two cores, or computing engines, in one physical processor. This enables dual-core processors to simultaneously execute two computing tasks, which is advantageous in multitasking environments, such as Windows XP, where multiple applications run simultaneously. Two applications, such as NI LabVIEW and Microsoft Excel, each execute on a separate core at the same time. This improves overall system performance. Multithreaded applications, such as LabVIEW, take full advantage of dual-core processors because they separate their tasks into independent threads. A dual-core processor can simultaneously execute two of these threads.



Figure 1. This NI PXIe-8105 controls an 8-slot PXI Express modular instrumentation and data acquisition system.

## 2.0 GHz Dual-Core Embedded Controller for PXI Express

### Hardware

With state-of-the-art packaging, the NI PXIe-8105 embedded controller integrates the Intel Core Duo processor T2500 and all standard and extended PC I/O ports into a single unit. By integrating many I/O ports on the controller, all active slots in the PXI Express chassis remain available for measurement modules. This rugged one-piece controller design minimizes integration issues and eliminates the need for complex cabling to daughter boards. The NI PXIe-8105 also uses the Mobile Intel 945GM Express chipset to deliver maximum performance, flexibility, and stability. A block diagram of the NI PXIe-8105 is shown in Figure 2.

### Peripheral I/O

The NI PXIe-8105 includes high-performance peripheral I/O such as 10/100/1000BASE-TX (gigabit) Ethernet and four Hi-Speed USB ports for connection to a keyboard, a mouse, a CD-ROM/DVD-ROM drive for software installation, or other standard PC peripherals such as speakers, printers, or memory sticks. Use the IEEE 1284 ECP/EPP parallel port to connect to a wide variety of devices, including tape backup drives, printers, and scanners. An RS232 port is available for connecting to serial devices. Additionally, the NI PXIe-8105 includes an integrated GPIB (IEEE 488) controller, which provides control of external instrumentation, saving additional cost and a slot.

### ExpressCard

The NI PXIe-8105 includes an ExpressCard/34 slot. ExpressCard uses the PCI Express and Hi-Speed USB serial interfaces to provide up to 2.5 Gb/s of bidirectional throughput. Use the ExpressCard/34 slot to add a second gigabit Ethernet port to your system or additional peripheral I/O such as external SATA hard drives, 802.11 wireless LAN, IEEE 1394, Bluetooth, or various memory adapters.

### Video

The NI PXIe-8105 features the integrated Intel Graphics Media Accelerator 950, which delivers intense, realistic 3D graphics with sharp images, fast rendering, smooth motion, and high detail, without the need for an additional video card or peripheral. This unique architecture provides balanced memory usage between graphics and the system for optimal performance. Additionally, the NI PXIe-8105 includes a DVI-I video connector, compatible with digital (DVI) and analog (VGA) monitors. A DVI-I to VGA adapter is included with the controller for use with VGA monitors.

### Memory

The NI PXIe-8105 uses dual-channel 667 MHz DDR2 SDRAM. This feature makes the controllers ideal for data-intensive applications requiring significant analysis. The NI PXIe-8105 has two SO-DIMM sockets for the




Figure 2. NI PXIe-8105 Block Diagram

DDR2 SDRAM. 512 MB (1 x 512 MB DIMM) of RAM is standard with the NI PXIe-8105, with upgrade options to either 1, 2, 3, or 4 GB.

### Extended Temperature Option

The NI PXIe-8105 is available in two versions to address different environmental conditions. The basic version has an operating temperature of 5 to 50 °C and a storage temperature of -40 to 65 °C. The extended-temperature version has an operating temperature of 0 to 55 °C and a storage temperature of -40 to 71 °C. The primary difference is that the extended-temperature option uses a hard drive designed for reliability in low- and high-temperature extremes. This extended temperature hard drive has a capacity of 30 GB (minimum) versus 60 GB (minimum) on the standard controller. See specifications for further details.

### Software

The NI PXIe-8105 comes with the following minimum set of software already installed:

- Microsoft Windows XP Professional OS (contact National Instruments or visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor) for localized versions of Windows XP and for other available operating systems)
- Hard drive-based recovery image
- NI-VISA and NI-488.2 drivers
- Drivers for all built-in I/O ports (Table 1)

## 2.0 GHz Dual-Core Embedded Controller for PXI Express

With NI Factory Installation Services (FIS) added to a PXI Express system order, your embedded controller is shipped already configured with all software and drivers applicable for your system. For example, assume you order a PXI Express system that includes LabVIEW and NI TestStand software, as well as data acquisition modules, a digitizer, an arbitrary waveform generator, and a digital multimeter (DMM). With FIS, NI not only assembles and tests your system but also fully configures the embedded controller with the appropriate NI-DAQmx, NI-SCOPE, NI-FGEN, and NI-DMM drivers, as well as LabVIEW and NI TestStand. Additionally, your embedded controller is configured with a hard drive-based recovery image, so you can restore your controller to the as-shipped configuration at any time. This combination of software configuration and recovery tools provides both a productive and reliable development experience with your PXI Express system out of the box. To configure a complete PXI Express system with FIS, contact National Instruments or visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor).

## USB Peripherals

National Instruments offers a USB-to-dual-PS/2 keyboard/mouse adapter cable to connect a legacy PS/2 keyboard and mouse to a single USB port on your embedded controller. Additionally, NI offers external USB CD-ROM/DVD-ROM and USB floppy drives for use with your embedded controller. Using the USB interfaces, connect these drives to your embedded controller for easy software installation and upgrades. Both are completely powered through the USB port, so no external power connections are required. Additional USB peripherals, such as USB speakers to add audio or USB memory sticks to add easily removable memory, are widely available from PC peripheral manufacturers.

## Additional Peripheral Ports

National Instruments offers numerous plug-in modules to add more peripherals and ports to your PXI Express system. With the wide variety of peripheral devices available, you can choose modules that add communication with serial, IEEE 1394, and SCSI, in addition to numerous others. You also can obtain modules for controlling other PXI or VXI/VME systems. Visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor) to configure a system with additional peripheral modules.

### Ordering Information

For online configuration of a complete PXI Express system, including Factory Installation Services, visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor).

#### Step 1. Controller Model – select one of the following.

NI PXIe-8105	
Base .....	779710-xx
Extended Temperature .....	779711-xx

#### Step 2. Replace “xx” to select installed OS.

01.....	Windows XP Professional (English)
00.....	Localized Windows XP or Other OS <sup>1</sup>

<sup>1</sup>Contact National Instruments or visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor) for the latest operating systems.

#### Step 3. Memory upgrades – select the amount of upgrade memory.

Standard:	
512 MB (1 x 512 MB DIMM)	
Recommended upgraded memory configurations:	
1 GB (1 x 512 MB DIMM must be purchased)	
2 GB (2 x 1 GB DIMMs must be purchased)	
4 GB (2 x 2 GB DIMMs must be purchased)	
512 MB DDR2 RAM .....	779302-512
1 GB DDR2 RAM.....	779302-1024
2 GB DDR2 RAM.....	780031-2048

#### Step 4. Accessories<sup>2</sup>

USB-to-dual-PS/2 keyboard/mouse adapter cable .....	778713-02
External USB CD-ROM/DVD-ROM drive .....	778492-01
External USB floppy drive.....	778492-02
Spare DVI-I to VGA adapter.....	778713-03
Parallel port adapter cable (6 in.).....	777169-01
Micro-GPIB to GPIB adapter cable (0.2 m) .....	183285-0R2
Micro-GPIB to GPIB cable (1 m) .....	183285-01
Micro-GPIB to GPIB cable (2 m) .....	183285-02
ExpressCard strain-relief accessory	
for embedded controller.....	192524-01
USB English keyboard and optical mouse .....	779660-01
Flat panel monitor with VGA input .....	779559-01
NI FPT-1015 15 in. flat panel touch screen with	
VGA interface and USB .....	779560-01

<sup>2</sup>For additional peripheral modules, including serial, IEEE 1394, and SCSI, visit [ni.com/pxiadvisor](http://ni.com/pxiadvisor).

### BUY NOW!

For complete product specifications, pricing, and accessory information, call 800 813 3693 (U.S.) or go to [ni.com/pxi](http://ni.com/pxi).

## 2.0 GHz Dual-Core Embedded Controller for PXI Express

### Specifications

Specifications subject to change without notice.

#### Features

Processor .....	Intel Core Duo processor T2500 (2.0 GHz dual core)
Chipset .....	Mobile Intel 945GM Express chipset
Ethernet.....	10/100/1000BASE-TX, RJ45 connector
Video .....	Intel Graphics Media Accelerator 950
Serial .....	1 (RS232)
Parallel Port.....	IEEE 1284 Type C connector (miniature) (adapter cable not included)
GPIO .....	PCI-GPIO/TNT, micro D25 connector IEEE 488 and HS488 transfers (adapter cable not included)
Hi-Speed USB .....	4
RAM .....	2 SO-DIMM sockets, DDR2 SDRAM, PC2 5400, dual channel 512 MB (1 x 512 DIMM) standard, 4 GB (2 x 2 GB DIMMs) maximum
Hard Drive	
Base .....	60 GB minimum, internal 2.5 in., 9.5 mm Serial ATA 1.0 interface
Extended Temperature Option.....	30 GB minimum, internal 2.5 in., 9.5 mm Fast Ultra ATA100 interface
V (I/O) Keying .....	Chassis V (I/O) = +5 VDC (blue key)

#### PXI Express Link Configurations

PXI Express 4-link configuration.....	3 x4 links and 1 x1 link
PXI Express 2-link configuration.....	2 x4 links

#### Power Requirements

Voltage (V)	Current (A)	
	Typical	Maximum
+3.3	2	3.5
+5	1.5	3
+5_STBY	0.6	1
+12	1.5	3.75
-12	0	0

#### Physical

Board dimensions .....	4-slot 3U PXI Express module
Slot requirements .....	1 system slot, 3 controller expansion slots
Compatibility.....	Fully compatible with PXI Express Specification 1.0
Weight.....	0.97 kg (2.14 lb) typical

#### Environment

Maximum altitude.....	2,000 m (800 mbar) (at 25 °C ambient temperature)
Pollution degree.....	2
For indoor use only.	

#### Operating Environment

Ambient temperature	
Base.....	5 to 50 °C (tested in accordance with IEC-60068-2-1 and IEC-60068-2-2; meets MIL-PRF-28800F Class 3 high temperature limit)
Extended temperature.....	0 to 55 °C (tested in accordance with IEC-60068-2-1 and IEC-60068-2-2; meets MIL-PRF-28800F Class 3 low temperature limit and MIL-PRF-28800F Class 2 high temperature limit)
Relative humidity.....	10 to 90% noncondensing (tested in accordance with IEC-60068-2-56)

## 2.0 GHz Dual-Core Embedded Controller for PXI Express

---

### Storage Environment

Ambient temperature	
Base.....	-40 to 65 °C (tested in accordance with IEC-60068-2-1 and IEC-60068-2-2; meets MIL-PRF-28800F Class 3 low temperature limit)
Extended temperature.....	-40 to 71 °C (tested in accordance with IEC-60068-2-1 and IEC-60068-2-2; meets MIL-PRF-28800F Class 3 limits)
Relative humidity.....	5 to 95% noncondensing (tested in accordance with IEC-60068-2-56)

### Shock and Vibration

Operational shock.....	30 g peak, half-sine, 11 ms pulse (tested in accordance with IEC-60068-2-27; meets MIL-PRF-28800F Class 2 limits)
Random vibration	
Operating.....	5 to 500 Hz, 0.3 g <sub>rms</sub> (with solid-state hard drive)
Nonoperating.....	5 to 500 Hz, 2.4 g <sub>rms</sub> (tested in accordance with IEC-60068-2-64; nonoperating test profile exceeds the requirements of MIL-PRF-28800F, Class 3)

**Note:** Specifications subject to change without notice.

### Safety Compliance

EN 61010-1, IEC 61010-1, UL 61010-01, CSA 61010-1

### Electromagnetic Compatibility

Refer to the Declaration of Conformity (DoC) for regulatory compliance information.

To obtain the DoC for this product, click Declaration of Conformity at [ni.com/certification](http://ni.com/certification).

# NI Services and Support



NI has the services and support to meet your needs around the globe and through the application life cycle – from planning and development through deployment and ongoing maintenance. We offer services and service levels to meet customer requirements in research, design, validation, and manufacturing. Visit [ni.com/services](http://ni.com/services).

## Training and Certification

NI training is the fastest, most certain route to productivity with our products. NI training can shorten your learning curve, save development time, and reduce maintenance costs over the application life cycle. We schedule instructor-led courses in cities worldwide, or we can hold a course at your facility. We also offer a professional certification program that identifies individuals who have high levels of skill and knowledge on using NI products. Visit [ni.com/training](http://ni.com/training).

## Professional Services

Our NI Professional Services team is composed of NI applications and systems engineers and a worldwide National Instruments Alliance Partner program of more than 600 independent consultants and

integrators. Services range from start-up assistance to turnkey system integration. Visit [ni.com/alliance](http://ni.com/alliance).



## OEM Support

We offer design-in consulting and product integration assistance if you want to use our products for OEM applications. For information about special pricing and services for OEM customers, visit [ni.com/oem](http://ni.com/oem).

## Local Sales and Technical Support

In offices worldwide, our staff is local to the country, giving you access to engineers who speak your language. NI delivers industry-leading technical support through online knowledge bases, our applications engineers, and access to 14,000 measurement and automation professionals within NI Developer Exchange forums. Find immediate answers to your questions at [ni.com/support](http://ni.com/support).

We also offer service programs that provide automatic upgrades to your application development environment and higher levels of technical support. Visit [ni.com/ssp](http://ni.com/ssp).

## Hardware Services

### NI Factory Installation Services

NI Factory Installation Services (FIS) is the fastest and easiest way to use your PXI or PXI/SCXI combination systems right out of the box. Trained NI technicians install the software and hardware and configure the system to your specifications. NI extends the standard warranty by one year on hardware components (controllers, chassis, modules) purchased with FIS. To use FIS, simply configure your system online with [ni.com/pxiadvisor](http://ni.com/pxiadvisor).

### Calibration Services

NI recognizes the need to maintain properly calibrated devices for high-accuracy measurements. We provide manual calibration procedures, services to recalibrate your products, and automated calibration software specifically designed for use by metrology laboratories. Visit [ni.com/calibration](http://ni.com/calibration).

### Repair and Extended Warranty

NI provides complete repair services for our products. Express repair and advance replacement services are also available. We offer extended warranties to help you meet project life-cycle requirements. Visit [ni.com/services](http://ni.com/services).



[ni.com](http://ni.com) • 800 813 3693

National Instruments • [info@ni.com](mailto:info@ni.com)

