



- 9 MAX COMPONENT HEIGHT DOES NOT INCLUDE MATED CABLES.
- 8 IT IS RECOMMENDED THAT ADJACENT PCB'S AND SURFACES BE KEPT .300 [7.62] FROM THE SECONDARY SIDE SURFACE.
- 7 IT IS RECOMMENDED THAT ADJACENT PCB'S AND SURFACES BE KEPT .750 [19.05] FROM THE PRIMARY SIDE SURFACE.
- 6 RECOMMENDED PANEL THICKNESS RANGE IS FROM .032 [0.81] TO .100 [2.54].
- 5 4-40 MAX TORQUE 3.6 IN LBS.
- 4 DAUGHTER CARD COMPONENTS SHOULD NOT EXTEND ABOVE THIS KEEPOUT LINE.
- 3 HOLES AND KEEPOUTS SIZED FOR M3 STANDOFF (4.5 HEX) OR 4-40 STANDOFF (0.1875 HEX). MAX SCREW HEAD OR STANDOFF DIAMETER OF 0.236 [6 MM].
- 2 LATCH ON MATING PLUG REQUIRES CLEARANCE UP TO THIS HEIGHT.

1. REFER TO PRODUCT MANUAL ON NI.COM FOR MORE DETAILS.
 NOTES: UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN INCHES AND
 [MILLIMETERS].

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

NATIONAL INSTRUMENTS® AUSTIN, TEXAS	
TITLE	
CUSTOMER DRAWING, sbRIO-9623	
SIZE CODE IDENT NO MM/DD/YYYY	
D 7U296	03/14/2012
SCALE: 1/1	SHEET 1 OF 2

