



UNAMPLIFIED

COLOR	DESIGNATION
RED	(+)EXCITATION
BLACK	(-)EXCITATION
GREEN	(-)OUTPUT
WHITE	(+)OUTPUT

BALANCE & T.C.
MODULE

3 FEET OF 30 AWG.,
TEFLON INSULATED
COLOR CODED TWISTED LEADS

2 FT. OF SHIELDED
CABLE FROM LOAD CELL
TO BALANCE MODULE

A	REDRAWN PER ECN #	01-09-96 RH	
REV	DESCRIPTION	REVISED BY	APPROV. RELEASE
SCALE: NONE	DRAWN 1-8-85	SR	CHECKED: APPROVED: J H M 10/23/96

SENSOTEC INC. 1200 CHESAPEAKE AVE. COLUMBUS, OHIO 43212	
LOAD CELL, MODEL 13, 350 TO 1,000 LBS.	
.X ±.01	63
.XXX ±.005	DOCUMENT NUMBER
±1/2'	SHEET 1 OF 1
	000-1760-00