



SPECIFICATIONS:  
 AVAILABLE RANGE: 0 to 2,000 THRU 0 to 10,000 PSI  
 OUTPUT: 3 mv/v  
 EXCITATION: 10 VDC  
 TEMPERATURE COMPENSATED: 60 to 160 DEF.F.  
 OPERATING TEMPERATURE: -100 to 325 DEG.F.  
 OVERALL ACCURACY:  
     MODEL TJE = +/- 0.1% F.S.  
     Z = +/- 0.25% F.S.  
     A-5 = +/- 0.5% F.S.  
 WETTED MATERIAL: 15-5 PH S.S.

WIRING CODE  
 UNAMP (S) 6-PIN, 6-COND  
 PIN A & B = (+) EXCITATION  
 C & D = (-) EXCITATION  
 E = (-) OUTPUT  
 F = (+) OUTPUT

IF THIS IS A PAPER COPY IT IS UNCONTROLLED. VERIFY REVISION BEFORE USE.

PROPRIETARY RIGHTS NOTICE: THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN INCHES. INTERPRET PER ASME Y14.100-2000 OTHER HONEYWELL STDS MAY APPLY. ALL FILLETS & CORNERS .005R MAX DEBURR & BREAK SHARP CORNERS		-		INITIAL RELEASE TO PRODUCTION		-	-	-
REV	DESCRIPTION				REV BY	CHK BY	APV BY	
DRW: DILLON	CHK: FRESCO	MFG: FRESCO	ENG: RICHARDS					
AUTOCAD		10/17/1977	12/05/2003	12/05/2003	12/02/2003			
REV HIST	DO NOT SCALE							
	.X ±.2	HONEYWELL SENSOTEC 2080 ARLINGATE LANE COLUMBUS, OHIO 43228 www.honeywell.com/sensing						
	.XX ±.02	PRESSURE TRANSDUCER						
	.XXX ±.010	1.5" DIA HIGH CAPACITY						
		CODE IDENT NO. 51518		DOCUMENT NUMBER				
		SHEET 1 OF 1		SIZE A		000-0663-00		