



- 7 MAX COMPONENT HEIGHT DOES NOT INCLUDE MATED CABLES.
 - 6 RECOMMENDED PANEL THICKNESS RANGE IS FROM .032 [0.81] TO .100 [2.54].
 - 5 4-40 MAX TORQUE 3.6 IN LBS.
 - 4 DAUGHTER CARD COMPONENTS SHOULD NOT EXTEND ABOVE THIS KEEPOUT LINE.
 - 3 HOLES AND KEEPOUTS SIZED FOR M3 STANDOFF (4.5 HEX) OR 4-40 STANDOFF (0.1875 HEX). MAX SCREW HEAD OR STANDOFF DIAMETER OF 0.236 [6 MM].
 - 2 LATCH ON MATING PLUG REQUIRES CLEARANCE UP TO THIS HEIGHT.
1. REFER TO PRODUCT MANUAL ON NI.COM FOR MORE DETAILS.
 NOTES: UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND [MILLIMETERS].	NATIONAL INSTRUMENTS® AUSTIN, TEXAS	
	TITLE CUSTOMER DRAWING, sbRIO-9627	
DO NOT SCALE DRAWING THIRD ANGLE PROJECTION	SIZE CODE IDENT NO. MM/DD/YYYY D 7U296 09/25/2015	
	SCALE: 1/1	SHEET 1 OF 2

CU.SBR10-9627

