



- 7 MAX COMPONENT HEIGHT DOES NOT INCLUDE MATED CABLES.
 - 6 RECOMMENDED PANEL THICKNESS RANGE IS FROM .032 [0.81] TO .100 [2.54].
 - 5 4-40 MAX TORQUE 3.6 IN LBS.
 - 4 DAUGHTER CARD COMPONENTS SHOULD NOT EXTEND ABOVE THIS KEEP-OUT LINE.
 - 3 HOLES AND KEEPOUTS SIZED FOR M3 STANDOFF (4.5 HEX) OR 4-40 STANDOFF (0.1875 HEX). MAX SCREW HEAD OR STANDOFF DIAMETER OF 0.236 [6 MM].
 - 2 LATCH ON MATING PLUG REQUIRES CLEARANCE UP TO THIS HEIGHT.
1. REFER TO PRODUCT MANUAL ON NI.COM FOR MORE DETAILS
- NOTES: UNLESS OTHERWISE SPECIFIED.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND [MILLIMETERS]. DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 	NATIONAL INSTRUMENTS® AUSTIN, TEXAS
	TITLE CUSTOMER DRAWING, sbRIO-9637
	SIZE CODE IDENT NO. MM/DD/YYYY D 7U296 09/25/2015 SCALE: 2.000 SHEET 1 OF 2 CU.SBR10-9637

