

## SPECIFICATIONS

# PCIe-4065

PCI Express, 6½-Digit, ±300 V Digital Multimeter Device

These specifications apply to the PCIe-4065.

## Contents

---

Definitions.....	1
Conditions.....	2
DC Specifications.....	2
DC System Speed Characteristics.....	3
DC Accuracy Specifications.....	3
DC Functions General Specifications.....	5
AC Specifications.....	6
AC System Speed Characteristics.....	6
AC Accuracy Specifications.....	6
AC Functions General Specifications.....	7
Temperature Accuracy Specifications.....	8
General Specifications.....	9
Input Protection Characteristics.....	10
Calibration Interval.....	10
Warm-Up Time Characteristics.....	10
Trigger Characteristics.....	10
Power Consumption Characteristics.....	11
Physical Characteristics.....	11
Environment.....	11
Operating Environment.....	11
Storage Environment.....	11
Compliance and Certifications.....	11
Safety.....	12
Electromagnetic Compatibility.....	12
CE Compliance.....	12
Online Product Certification.....	13
Environmental Management.....	13

## Definitions

---

*Warranted* specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

*Characteristics* describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- *Typical* specifications describe the expected performance met by a majority of the models.
- *Nominal* specifications describe parameters and attributes that may be useful in operation.

Specifications are *Warranted* unless otherwise noted.

## Conditions


Specifications are valid under the following conditions unless otherwise noted.

- Ambient temperature of  $T_{cal} \pm 5 \text{ }^\circ\text{C}$ .<sup>1</sup>
- Calibration interval of 1 year
- 30 minutes minutes warm-up time
- **niDMM Digits Resolution** property or NIDMM\_ATTR\_RESOLUTION\_DIGITS attribute set to 6.5
- **niDMM Aperture Time Units** property or NIDMM\_ATTR\_APERTURE\_TIME\_UNITS attribute set to Power Line Cycles
- **niDMM Aperture Time** property or NIDMM\_ATTR\_APERTURE\_TIME attribute set to 10

## DC Specifications

Resolution (digits)	Reading rate (S/s), specified for 60 Hz (and 50 Hz) operation	Aperture time (NPLC)	RMS noise (ppm of range), 10 V range
6½	0.6 (0.5)	100	0.06
	6 (5)	10	0.2
	10 (8.33)	6	0.25
5½	30 (25)	2	0.4
	60 (50)	1	0.55
	900	0.06	1.7
	1,500	0.04	2.5
4½	3,000	0.02	11.5

<sup>1</sup>  $T_{cal}$  = temperature at which last external calibration was performed. NI factory calibration is  $23 \text{ }^\circ\text{C} \pm 1 \text{ }^\circ\text{C}$ .

**Figure 1. Noise Performance<sup>2</sup>**

## DC System Speed Characteristics

Range or function changes	10/s
Auto Range time, DC V	200 ms
Auto Range time, DC I	200 ms
Auto Range time, resistance	250 ms
Trigger latency	<1 $\mu$ s
Maximum trigger rate	2.5 kHz

## DC Accuracy Specifications

**Table 1. DC Voltage  $\pm$  (ppm of Reading + ppm of Range)**

Range	Resolution	Input resistance (10 M $\Omega$ , default), nominal	24 Hr <sup>4</sup> T <sub>cal</sub> <sup>5</sup> $\pm$ 1 $^{\circ}$ C	90 day T <sub>cal</sub> $\pm$ 5 $^{\circ}$ C	1 year T <sub>cal</sub> $\pm$ 5 $^{\circ}$ C	Tempco <sup>6</sup> (ppm/ $^{\circ}$ C)
100 mV <sup>3</sup>	100 nV	>10 G $\Omega$ , 10 M $\Omega$	30 + 30	65 + 35	90 + 35	5 + 2
1 V	1 $\mu$ V	>10 G $\Omega$ , 10 M $\Omega$	20 + 8	65 + 12	90 + 12	5 + 1
10 V	10 $\mu$ V	>10 G $\Omega$ , 10 M $\Omega$	15 + 7	65 + 12	90 + 12	5 + 1

<sup>2</sup> Measured on the 10 V range.

<sup>3</sup> With offset nulling.

**Table 1. DC Voltage ± (ppm of Reading + ppm of Range) (Continued)**

Range	Resolution	Input resistance (10 MΩ, default), nominal	24 Hr <sup>4</sup> T <sub>cal</sub> <sup>5</sup> ±1 °C	90 day T <sub>cal</sub> ±5 °C	1 year T <sub>cal</sub> ±5 °C	Tempco <sup>6</sup> (ppm/°C)
100 V	100 μV	10 MΩ	20 + 8	75 + 12	110 + 12	9 + 1
300 V	1 mV	10 MΩ	20 + 24	75 + 40	110 + 40	9 + 1

**Table 2. DC Current ± (ppm of Reading + ppm of Range)**

Range	Resolution	Burden voltage, typical	24 Hr <sup>4</sup> T <sub>cal</sub> <sup>5</sup> ±1 °C	90 day T <sub>cal</sub> ±5 °C	1 year T <sub>cal</sub> ±5 °C	Tempco <sup>6</sup> (ppm/°C)
10 mA	10 nA	<60 mV	50 + 100	300 + 200	500 + 200	30 + 20
100 mA	100 nA	<0.6 V	100 + 40	300 + 50	500 + 50	30 + 5
1 A	1 μA	<0.35 V	500 + 60	800 + 100	1,000 + 100	65 + 10
3 A	3 μA	<1 V	1,000 <sup>7</sup> + 200	1,200 <sup>7</sup> + 200	1,200 <sup>7</sup> + 200	65 + 20

<sup>4</sup> Relative to external calibration source. DMM must remain powered on.

<sup>5</sup> T<sub>cal</sub> is the temperature at which last external calibration was performed. NI factory calibration is 23°C ±1°C.

<sup>6</sup> Tempco is the temperature coefficient in ppm of range per degree Celsius.

<sup>7</sup> Add 650 ppm/A of reading for currents above 1.5 A.

**Table 3. Resistance<sup>8</sup> (4-Wire and 2-Wire) ± (ppm of Reading + ppm of Range)**

Range	Resolution	Test current, nominal	24 Hr <sup>9</sup> T <sub>cal</sub> <sup>10</sup> ±1 °C	90 day T <sub>cal</sub> ±5 °C	1 year T <sub>cal</sub> ±5 °C	Tempco <sup>6</sup> (ppm/°C)
100 Ω	100 μΩ	1 mA	30 + 30	95 + 40	110 + 40	8 + 3
1 kΩ	1 mΩ	1 mA	20 + 8	95 + 20	110 + 20	8 + 1
10 kΩ	10 mΩ	100 μA	20 + 8	95 + 20	110 + 20	8 + 1
100 kΩ	100 mΩ	10 μA	20 + 8	95 + 20	110 + 20	8 + 1
1 MΩ	1 Ω	5 μA	20 + 12	110 + 24	125 + 24	10 + 1
10 MΩ <sup>11</sup>	10 Ω	500 nA	150 + 12	400 + 24	500 + 24	30 + 2
100 MΩ <sup>11</sup>	100 Ω	500 nA   10 MΩ	2,000 + 24	6,000 + 60	8,000 + 60	400 + 4

**Table 4. Diode Test<sup>12</sup>**

Range	Resolution	Test current, nominal	Accuracy
10 V	10 μV	100 μA, 1 mA (up to 3.5 V measurement for 1 mA test current)	Add 50 ppm of range and 50 ppm of reading to 10 V DC voltage specifications.

## DC Functions General Specifications

Overrange	105% of range except 300 V and 3 A range
Maximum 4-wire lead resistance	Use the lesser of 10% of range or 1 kΩ
DC voltage input bias current	<40 pA at 23 °C, typical
Effective Common-Mode Rejection Ratio (CMRR)	>150 dB second order DC noise rejection (for power-line frequency ±0.1%), 12 PLC aperture
(1 kΩ resistance in LO lead)	

<sup>8</sup> Specifications are for 4-wire measurements. For 2-wire measurements, perform offset nulling or add 200 mΩ to specification. For relative humidity >80%, add 100 ppm/MΩ.

<sup>9</sup> Relative to external calibration source. DMM must remain powered on.

<sup>10</sup> T<sub>cal</sub> is the temperature at which last external calibration was performed. NI factory calibration is 23°C ±1°C.

<sup>11</sup> 2-wire resistance measurement only.

<sup>12</sup> Can be used to test p-n junctions, LEDs, or zener diodes up to 10 V.

**Table 5. Normal Mode Rejection Ratio (NMRR)**

Aperture time (NPLC)	DC noise rejection	Normal mode rejection (for power-line frequency $\pm 0.1\%$ )
1	Normal	60 dB
2	Second-order	>85 dB
10		

## AC Specifications

Desired bandwidth	Recommended reading rate	Resolution (digits)
10 Hz to 100 kHz	1 S/s	6½
100 Hz to 100 kHz	10 S/s	5½
500 Hz to 100 kHz	100 S/s	4½

## AC System Speed Characteristics

Range or function changes	10/s
Trigger latency	<1 $\mu$ s
Maximum trigger rate	2.5 kHz

## AC Accuracy Specifications



**Note** All AC accuracy specifications apply to signal amplitudes greater than 2% of range.

**Table 6. AC Voltage (% of Reading + % of Range)**

Range (peak voltage)	Frequency	24 hr <sup>13</sup> T <sub>cal</sub> ±1 °C	1 year <sup>14</sup> T <sub>cal</sub> ±5 °C	Tempco <sup>15</sup> (%/°C)
200 mV (± 320 mV), 2 V (± 3.2 V), 20 V (± 32 V), 300 V (± 425 V)	10 Hz to 40 Hz	1.5 + 0.04	2 + 0.05	0.01 + 0.003
	> 40 Hz to 20 kHz	0.2 + 0.04	0.2 + 0.05	0.01 + 0.003
	> 20 kHz to 50 kHz	0.3 + 0.04	0.3 + 0.05	0.01 + 0.003
	> 50 kHz to 100 kHz	1.5 + 0.08	1.5 + 0.08	0.02 + 0.005

**Table 7. AC Current (% of Reading + % of Range)**

Range (peak current)	Frequency	24 hr <sup>13</sup> T <sub>cal</sub> ±1 °C	1 year <sup>14</sup> T <sub>cal</sub> ±5 °C	Tempco <sup>15</sup> (%/°C)
10 mA (± 16 mA), 100 mA (± 160 mA), 500 mA (± 780 mA), 3 A (± 4.25 A)	10 Hz to 40 Hz	1.6 to 0.05	2.1 + 0.05	0.015 + 0.03
	> 40 Hz to 5 kHz	0.3 + 0.05	0.3 + 0.06	0.015 + 0.03

**Table 8. High Crest Factor Additional Error<sup>16</sup>**

Crest factor	Additional error (% of reading)
1 to 3	0.05%
3 to 4	0.1%
4 to 5	1% (for frequencies above 2 kHz)

## AC Functions General Specifications

Input impedance 10 MΩ in parallel with 200 pF, nominal

Input coupling AC coupling

Maximum Voltz-Hertz product  $3 \times 10^7$  V-Hz

Maximum DC voltage component 250 V

<sup>13</sup> T<sub>cal</sub> is the temperature at which last external calibration was performed. NI factory calibration is 23°C ±1 °C.

<sup>14</sup> Use the 1 Year specification to calibrate on a 90-day cycle.

<sup>15</sup> Tempco is the temperature coefficient. Tempco values are valid within the device's ambient temperature range.

<sup>16</sup> Applicable for non-sinewave signals up to the rated peak voltage, current, or bandwidth.

## Temperature Accuracy Specifications<sup>17</sup>

**Table 9.** Thermocouple Temperature Accuracy Specifications ( $^{\circ}\text{C}$ )

Type	Range	1 year $T_{\text{cal}} \pm 5^{\circ}\text{C}$		Tempco ( $^{\circ}\text{C}_{\text{reading}}/^{\circ}\text{C}_{\text{DMM}}$ ) <sup>20</sup>	Resolution
		With Simulated Ref. Junction <sup>18</sup>	With PXI-2527 <sup>19</sup>		
J	-150 to 1200	0.3	1.0	0.03	0.1
	-210 to -150	0.4	1.2	0.03	0.1
K	-100 to 1200	0.4	1.0	0.03	0.1
	-200 to -100	0.4	1.5	0.03	0.1
N	-100 to 1300	0.3	1.0	0.03	0.1
	-200 to -100	0.6	1.5	0.03	0.1
T	-100 to 400	0.3	1.0	0.03	0.1
	-200 to -100	0.4	1.5	0.03	0.1
E	-150 to 1000	0.2	1.0	0.03	0.1
	-200 to -150	0.3	1.5	0.03	0.1
R	300 to 1760	0.6	1.8	0.06	0.1
	-50 to 300	1.4	1.9	0.06	0.1
S	400 to 1760	0.7	1.8	0.06	0.1
	-50 to 400	1.3	1.8	0.06	0.1

<sup>17</sup>  $T_{\text{cal}}$  = temperature at which last external calibration was performed. NI factory calibration is  $23^{\circ}\text{C} \pm 1^{\circ}\text{C}$ . For total measurement accuracy, add temperature probe error.

<sup>18</sup> Using simulated reference junction.

<sup>19</sup> Includes PXI 2527 with TB 2627 with a typical  $0.5^{\circ}\text{C}$  CJC error and a typical thermal EMF offset of  $2.5\ \mu\text{V}$  for CJC temperatures between  $15^{\circ}\text{C}$  and  $35^{\circ}\text{C}$ . Add an additional  $0.5^{\circ}\text{C}$  uncertainty when CJC is in the range  $0^{\circ}\text{C}$  to  $15^{\circ}\text{C}$  or  $35^{\circ}\text{C}$  to  $50^{\circ}\text{C}$ .

<sup>20</sup> Tempco = Temperature coefficient, expressed in degrees of measurement uncertainty per degree change in DMM instrument operating temperature.



**Table 9.** Thermocouple Temperature Accuracy Specifications (°C) (Continued)

Type	Range	1 year $T_{cal} \pm 5 \text{ }^\circ\text{C}$		Tempco ( $^\circ\text{C}_{reading}/^\circ\text{C}_{DMM}$ ) <sup>20</sup>	Resolution
		With Simulated Ref. Junction <sup>18</sup>	With PXI-2527 <sup>19</sup>		
B	1100 to 1820	0.6	1.8	0.09	0.1
	400 to 1100	1.4	1.9	0.09	0.1

**Table 10.** RTD<sup>21</sup> Temperature Accuracy Specifications (°C)

Range	1 year $T_{cal}^{18} \pm 5 \text{ }^\circ\text{C}$	Tempco/ $^\circ\text{C}^{22}$	Resolution
-200 to 600	0.17	0.011	0.01

**Table 11.** Thermistor Temperature Accuracy Specifications (°C)

Range	1 year $T_{cal}^{18} \pm 5 \text{ }^\circ\text{C}$	Tempco/ $^\circ\text{C}^{22}$	Resolution
-80 to 150	0.08	0.002	0.01

## General Specifications

Maximum common-mode voltage 300 V AC<sub>rms</sub> or DC

Measurement Category II



**Caution** Do not use this device for connection to signals or for measurements within Measurement Categories III or IV.

<sup>18</sup> Using simulated reference junction.

<sup>19</sup> Includes PXI 2527 with TB 2627 with a typical 0.5 °C CJC error and a typical thermal EMF offset of 2.5 μV for CJC temperatures between 15 °C and 35 °C. Add an additional 0.5 °C uncertainty when CJC is in the range 0 °C to 15 °C or 35 °C to 50 °C.

<sup>21</sup> RTD with  $R_0 = 100 \text{ } \Omega$  Pt3851 RTD in a 4-wire configuration, using lowest possible resistance range for each temperature.

<sup>22</sup> Tempco is the temperature coefficient, expressed in degrees of measurement uncertainty per degree change in DMM instrument operating temperature.

## Input Protection Characteristics

DC I and AC I	3.15 Amp, fused F 3.15 A 250 V, fast-acting user-replaceable fuse
Resistance, diode	Up to 300 V DC
DC V, AC V	Up to 300 V DC, 300 V AC <sub>rms</sub> , 450 V AC peak



**Fuse** When this fuse symbol is marked on a device, take proper precautions.



**Hazardous Voltage** This icon denotes a warning advising you to take precautions to avoid electrical shock.

## Calibration Interval

Calibration interval	1 year recommended
----------------------	--------------------

## Warm-Up Time Characteristics

Warm-up time	30 minutes to rated accuracy
--------------	------------------------------

## Trigger Characteristics

### Input triggers

Types	Trigger, Sample Trigger (programmable edge)
Sources	Auxiliary connector (AUX I/O connector)
Minimum pulse width	200 ns
Max samples per trigger	$2.1 \times 10^9$
Trigger delay	0 to 149 s
Logic level	5 V TTL, LVTTTL

### Output triggers

Types	Measurement Complete (programmable edge)
Destinations	Auxiliary connector (AUX I/O connector)
Pulse width	1 $\mu$ s
Logic level	3.3 V



**Note** The AUX I/O connector is not isolated. It is not referenced to your measurement circuit. The connector is referenced to the ground of your chassis. The digital signals on this connector should not operate beyond -0.5 to 5.5 V of your chassis ground. The trigger signals are TTL-compatible.

# Power Consumption Characteristics

Power consumption <3 W from PCI Express motherboard

---

# Physical Characteristics

Dimensions One slot, PCI Express module  
18.3 cm × 2.0 cm × 12.0 cm  
(7.2 in. × 0.8 in. × 4.7 in.)

---

Weight 325 g (11.5 oz)

---

# Cleaning Statement



**Caution** Clean the hardware with a soft, nonmetallic brush. Make sure that the hardware is completely dry and free from contaminants before returning it to service.

# Environment

---

Maximum altitude 2,000 m (at 25 °C ambient temperature)

---

Pollution Degree 2

---

Indoor use only.

# Operating Environment

Ambient temperature range 0 to 40 °C (Tested in accordance with IEC 60068-2-1 and IEC 60068-2-2.)

---

Relative humidity range 10% to 90%, noncondensing

---

# Storage Environment

Ambient temperature range -40 °C to 70 °C (Tested in accordance with IEC 60068-2-1 and IEC 60068-2-2.)

---

Relative humidity range 5% to 95%, noncondensing (Tested in accordance with IEC 60068-2-56.)

---

# Compliance and Certifications

---



**Caution** You can impair the protection provided by the PCIe-4065 if you use it in a manner not described in this document.



**Caution** This product is intended for use in industrial locations. As a result, this product may cause interference if used in residential areas. Such use must be

avoided unless the user takes special measures to reduce electromagnetic emissions to prevent interference to the reception of radio and television broadcasts.

## Safety

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1



**Note** For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

## Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- EN 55022 (CISPR 22): Class A emissions
- EN 55024 (CISPR 24): Immunity
- AS/NZS CISPR 11: Group 1, Class A emissions
- AS/NZS CISPR 22: Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



**Note** In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia, and New Zealand (per CISPR 11), Class A equipment is intended for use only in heavy-industrial locations.



**Note** Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



**Note** For EMC declarations, certifications, and additional information, refer to the [Online Product Certification](#) section.

## CE Compliance

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)

## Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit [ni.com/certification](https://ni.com/certification), search by model number or product line, and click the appropriate link in the Certification column.

## Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *Minimize Our Environmental Impact* web page at [ni.com/environment](https://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

## Waste Electrical and Electronic Equipment (WEEE)



**EU Customers** At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit [ni.com/environment/weee](https://ni.com/environment/weee).

## 电子信息产品污染控制管理办法（中国 RoHS）



**中国客户** National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息，请登录 [ni.com/environment/rohs\\_china](https://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](https://ni.com/environment/rohs_china).)

Information is subject to change without notice. Refer to the *NI Trademarks and Logo Guidelines* at [ni.com/trademarks](http://ni.com/trademarks) for information on NI trademarks. Other product and company names mentioned herein are trademarks or trade names of their respective companies. For patents covering NI products/technology, refer to the appropriate location: **Help»Patents** in your software, the `patents.txt` file on your media, or the *National Instruments Patent Notice* at [ni.com/patents](http://ni.com/patents). You can find information about end-user license agreements (EULAs) and third-party legal notices in the `readme` file for your NI product. Refer to the *Export Compliance Information* at [ni.com/legal/export-compliance](http://ni.com/legal/export-compliance) for the NI global trade compliance policy and how to obtain relevant HTS codes, ECCNs, and other import/export data. NI MAKES NO EXPRESS OR IMPLIED WARRANTIES AS TO THE ACCURACY OF THE INFORMATION CONTAINED HEREIN AND SHALL NOT BE LIABLE FOR ANY ERRORS. U.S. Government Customers: The data contained in this manual was developed at private expense and is subject to the applicable limited rights and restricted data rights as set forth in FAR 52.227-14, DFAR 252.227-7014, and DFAR 252.227-7015.

© 2006—2017 National Instruments. All rights reserved.

376811A-01 Jan17